

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299480

Luminaire Tested: P3A17R20W2N902750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R20W2N902750DE010 E3CD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1508.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299480
CATALOG NUMBER: P3A17R20W2N902750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299480

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 116 | 114 | 112 | 110 | 113 | 112 | 110 | 109 | 108 | 106 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 99 | 98 | 98 | 98 |
| 2 | 112 | 109 | 107 | 104 | 110 | 108 | 105 | 103 | 104 | 103 | 101 | 102 | 100 | 99 | 99 | 98 | 97 | 99 | 98 | 97 | 95 |
| 3 | 109 | 105 | 102 | 100 | 108 | 104 | 101 | 99 | 102 | 99 | 97 | 99 | 98 | 96 | 97 | 96 | 95 | 97 | 96 | 95 | 93 |
| 4 | 107 | 102 | 99 | 96 | 105 | 101 | 98 | 96 | 99 | 97 | 95 | 97 | 95 | 93 | 96 | 94 | 92 | 96 | 94 | 92 | 91 |
| 5 | 104 | 99 | 96 | 93 | 103 | 98 | 95 | 93 | 97 | 94 | 92 | 95 | 93 | 91 | 94 | 92 | 91 | 94 | 92 | 91 | 90 |
| 6 | 102 | 97 | 93 | 91 | 101 | 96 | 93 | 90 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 90 | 89 | 93 | 90 | 89 | 88 |
| 7 | 100 | 94 | 91 | 88 | 99 | 94 | 91 | 88 | 93 | 90 | 88 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 89 | 87 | 86 |
| 8 | 98 | 92 | 89 | 86 | 97 | 92 | 89 | 86 | 91 | 88 | 86 | 90 | 88 | 86 | 89 | 87 | 85 | 89 | 87 | 85 | 85 |
| 9 | 96 | 90 | 87 | 85 | 95 | 90 | 87 | 85 | 89 | 86 | 84 | 89 | 86 | 84 | 88 | 86 | 84 | 88 | 86 | 84 | 83 |
| 10 | 94 | 89 | 85 | 83 | 93 | 88 | 85 | 83 | 88 | 85 | 83 | 87 | 84 | 83 | 86 | 84 | 82 | 86 | 84 | 82 | 82 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2342093 |
| 5° | 2032858 |
| 10° | 1256089 |
| 15° | 436279 |
| 20° | 133968 |
| 25° | 47374 |
| 30° | 17522 |
| 35° | 7040 |
| 40° | 3750 |
| 45° | 1489 |
| 50° | 819 |
| 55° | 918 |
| 60° | 1053 |
| 65° | 623 |
| 70° | 769 |
| 75° | 1017 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1489 cd/sqm



TEST NUMBER: P1299480

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CD1MW_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 766.5 | 50.8 |
| 10°-20° | 608.1 | 40.3 |
| 20°-30° | 105.3 | 7.0 |
| 30°-40° | 19.1 | 1.3 |
| 40°-50° | 4.4 | 0.3 |
| 50°-60° | 2.2 | 0.1 |
| 60°-70° | 1.3 | 0.1 |
| 70°-80° | 1.1 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1479.9 | 98.1 |
| 0°-40° | 1499.0 | 99.4 |
| 0°-60° | 1505.6 | 99.8 |
| 0°-90° | 1508.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1508.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 10681 | |
| 5° | 9235 | 766 |
| 15° | 1922 | 608 |
| 25° | 196 | 105 |
| 35° | 26 | 19 |
| 45° | 5 | 4 |
| 55° | 2 | 2 |
| 65° | 1 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1299480
CATALOG NUMBER: P3A17R20W2N902750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 10680.8 |
| 1° | 10629.5 |
| 2° | 10426.6 |
| 3° | 10100.7 |
| 4° | 9718.7 |
| 5° | 9235.3 |
| 6° | 8681.4 |
| 7° | 8036.9 |
| 8° | 7302.8 |
| 9° | 6478.0 |
| 10° | 5641.2 |
| 12.5° | 3558.3 |
| 15° | 1921.8 |
| 17.5° | 1026.5 |
| 20° | 574.1 |
| 22.5° | 328.3 |
| 25° | 195.8 |
| 27.5° | 119.4 |
| 30° | 69.2 |
| 32.5° | 40.6 |
| 35° | 26.3 |
| 37.5° | 17.9 |
| 40° | 13.1 |
| 42.5° | 8.4 |
| 45° | 4.8 |
| 47.5° | 2.4 |
| 50° | 2.4 |
| 52.5° | 2.4 |
| 55° | 2.4 |
| 57.5° | 2.4 |
| 60° | 2.4 |
| 62.5° | 1.2 |
| 65° | 1.2 |
| 67.5° | 1.2 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 1.2 |
| 77.5° | 1.2 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)