

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289662

Luminaire Tested: P3A05R40W2N902765DE010 E3DLP1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R40W2N902765DE010 E3DLP1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 263.0 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289662

CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1LI_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1289662

CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	95		105	101	97	93		97	94	91		94	92	89		92	89	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		86	84	81
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	73		81	76	72		79	75	71		77	74	71
6	87	78	72	68		86	78	72	68		76	71	67		75	70	67		73	69	66
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	62
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81901
5°	80233
10°	74704
15°	65108
20°	52481
25°	39341
30°	27650
35°	18123
40°	10963
45°	6543
50°	3923
55°	3135
60°	2807
65°	2439
70°	2308
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6543 cd/sqm

TEST NUMBER: P1289662

CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	12.9
10°-20°	79.0	30.0
20°-30°	74.4	28.3
30°-40°	43.0	16.4
40°-50°	17.1	6.5
50°-60°	7.6	2.9
60°-70°	4.7	1.8
70°-80°	2.5	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	187.3	71.2
0°-40°	230.3	87.6
0°-60°	255.1	97.0
0°-90°	263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	263.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	374	
5°	364	34
15°	287	79
25°	163	74
35°	68	43
45°	21	17
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1289662

CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	373.5
2.5°	371.3
5°	364.5
7.5°	352.0
10°	335.5
12.5°	313.3
15°	286.8
17.5°	257.1
20°	224.9
22.5°	192.6
25°	162.6
27.5°	134.6
30°	109.2
32.5°	87.0
35°	67.7
37.5°	51.2
40°	38.3
42.5°	28.6
45°	21.1
47.5°	15.4
50°	11.5
52.5°	9.3
55°	8.2
57.5°	7.5
60°	6.4
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.6
72.5°	2.9
75°	2.1
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)