

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289841

Luminaire Tested: P3A05R45W2N902765DE010 E3CD1MW\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289841  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R45W2N902765DE010 E3CD1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3CD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 481.0 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289841

CATALOG NUMBER: P3A05R45W2N902765DE010 E3CD1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289841

CATALOG NUMBER: P3A05R45W2N902765DE010 E3CD1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  |    |    |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 94  | 92  | 91  |    |    |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 91  | 94  | 91  | 89  | 92  | 90  | 88  | 86  |    |    |
| 4   | 102 | 95  | 91  | 87  | 100 | 94  | 90  | 87  | 92  | 89  | 86  | 90  | 87  | 85  | 88  | 86  | 84  | 82  |    |    |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  | 87  | 83  | 81  | 85  | 82  | 80  | 79  |    |    |
| 6   | 94  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  | 83  | 80  | 77  | 82  | 79  | 76  | 75  |    |    |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 78  | 74  | 81  | 77  | 74  | 80  | 76  | 74  | 79  | 76  | 73  | 72  |    |    |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |    |    |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 73  | 70  | 67  | 66  |    |    |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  | 71  | 67  | 65  | 71  | 67  | 65  | 64  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 208536 |
| 5°  | 209663 |
| 10° | 203203 |
| 15° | 170285 |
| 20° | 130165 |
| 25° | 79238  |
| 30° | 32967  |
| 35° | 10574  |
| 40° | 3292   |
| 45° | 682    |
| 50° | 478    |
| 55° | 535    |
| 60° | 482    |
| 65° | 571    |
| 70° | 449    |
| 75° | 593    |
| 80° | 505    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 682 cd/sqm

TEST NUMBER: P1289841

CATALOG NUMBER: P3A05R45W2N902765DE010 E3CD1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 89.8   | 18.7      |
| 10°-20°   | 206.2  | 42.9      |
| 20°-30°   | 148.4  | 30.9      |
| 30°-40°   | 30.9   | 6.4       |
| 40°-50°   | 2.8    | 0.6       |
| 50°-60°   | 1.2    | 0.2       |
| 60°-70°   | 0.9    | 0.2       |
| 70°-80°   | 0.6    | 0.1       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 444.4  | 92.4      |
| 0°-40°    | 475.3  | 98.8      |
| 0°-60°    | 479.3  | 99.6      |
| 0°-90°    | 481.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 481.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 951 |      |
| 5°  | 952 | 90   |
| 15° | 750 | 206  |
| 25° | 328 | 148  |
| 35° | 40  | 31   |
| 45° | 2   | 3    |
| 55° | 1   | 1    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1289841

CATALOG NUMBER: P3A05R45W2N902765DE010 E3CD1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 951.0 |
| 2.5°  | 951.4 |
| 5°    | 952.5 |
| 7.5°  | 945.6 |
| 10°   | 912.6 |
| 12.5° | 843.8 |
| 15°   | 750.1 |
| 17.5° | 654.3 |
| 20°   | 557.8 |
| 22.5° | 447.0 |
| 25°   | 327.5 |
| 27.5° | 216.0 |
| 30°   | 130.2 |
| 32.5° | 72.8  |
| 35°   | 39.5  |
| 37.5° | 22.2  |
| 40°   | 11.5  |
| 42.5° | 5.0   |
| 45°   | 2.2   |
| 47.5° | 1.4   |
| 50°   | 1.4   |
| 52.5° | 1.4   |
| 55°   | 1.4   |
| 57.5° | 1.1   |
| 60°   | 1.1   |
| 62.5° | 1.1   |
| 65°   | 1.1   |
| 67.5° | 0.7   |
| 70°   | 0.7   |
| 72.5° | 0.7   |
| 75°   | 0.7   |
| 77.5° | 0.4   |
| 80°   | 0.4   |
| 82.5° | 0.4   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)