

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299580

Luminaire Tested: P3A17R20W2N902750DE010 E3PHLP1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R20W2N902750DE010 E3PHLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 30.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299580
CATALOG NUMBER: P3A17R20W2N902750DE010 E3PHLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299580

CATALOG NUMBER: P3A17R20W2N902750DE010 E3PHLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	13.5
10°-20°	150.8	25.8
20°-30°	132.7	22.7
30°-40°	85.6	14.6
40°-50°	45.4	7.8
50°-60°	34.1	5.8
60°-70°	29.0	5.0
70°-80°	20.4	3.5
80°-90°	8.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.5	62.0
0°-40°	448.1	76.6
0°-60°	527.6	90.2
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	949	
5°	882	79
15°	542	151
25°	288	133
35°	134	86
45°	55	45
55°	38	34
65°	29	29
75°	19	20
85°	7	8
90°	0	



TEST NUMBER: P1299580
CATALOG NUMBER: P3A17R20W2N902750DE010 E3PHLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	948.7
2.5°	929.8
5°	881.6
7.5°	807.5
10°	723.1
12.5°	630.2
15°	542.4
17.5°	463.2
20°	396.0
22.5°	339.2
25°	287.5
27.5°	242.8
30°	203.2
32.5°	167.0
35°	134.3
37.5°	108.5
40°	86.1
42.5°	68.9
45°	55.1
47.5°	48.2
50°	43.0
52.5°	39.6
55°	37.9
57.5°	36.2
60°	34.4
62.5°	31.0
65°	29.3
67.5°	27.5
70°	24.1
72.5°	22.4
75°	18.9
77.5°	17.2
80°	13.8
82.5°	12.1
85°	6.9
87.5°	3.4
90°	0.0

(END OF REPORT)