

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289892

Luminaire Tested: P3A05R45W2N902765DE010 E3DLD1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R45W2N902765DE010 E3DLD1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 171.0 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289892
CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1289892

CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.1	8.8
10°-20°	37.7	22.0
20°-30°	44.8	26.2
30°-40°	38.9	22.8
40°-50°	19.5	11.4
50°-60°	6.8	4.0
60°-70°	4.7	2.8
70°-80°	2.7	1.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	97.6	57.1
0°-40°	136.5	79.8
0°-60°	162.8	95.2
0°-90°	171.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	171.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	165	
5°	162	15
15°	135	38
25°	98	45
35°	63	39
45°	25	20
55°	7	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1289892
CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	165.3
2.5°	164.6
5°	161.8
7.5°	157.5
10°	151.3
12.5°	143.9
15°	135.4
17.5°	125.9
20°	116.5
22.5°	106.8
25°	97.5
27.5°	88.7
30°	80.0
32.5°	71.7
35°	63.1
37.5°	53.8
40°	43.9
42.5°	34.3
45°	24.8
47.5°	16.4
50°	10.4
52.5°	8.1
55°	7.3
57.5°	6.7
60°	6.1
62.5°	5.5
65°	4.7
67.5°	4.1
70°	3.5
72.5°	3.0
75°	2.6
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)