

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299775

Luminaire Tested: P3A17R25W2N902750DE010 E3D1LI_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R25W2N902750DE010 E3D1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1463.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299775
CATALOG NUMBER: P3A17R25W2N902750DE010 E3D1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1299775

CATALOG NUMBER: P3A17R25W2N902750DE010 E3D1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1602262
5°	1484258
10°	1148387
15°	548516
20°	180849
25°	76238
30°	29549
35°	12769
40°	4265
45°	1985
50°	716
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1985 cd/sqm



TEST NUMBER: P1299775

CATALOG NUMBER: P3A17R25W2N902750DE010 E3D1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	592.7	40.5
10°-20°	674.1	46.1
20°-30°	156.7	10.7
30°-40°	32.9	2.2
40°-50°	5.3	0.4
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	97.3
0°-40°	1456.3	99.5
0°-60°	1462.5	100.0
0°-90°	1463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1463.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7307	
5°	6743	593
15°	2416	674
25°	315	157
35°	48	33
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1299775
CATALOG NUMBER: P3A17R25W2N902750DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	7306.9
1°	7292.0
2°	7216.2
3°	7109.6
4°	6946.7
5°	6743.0
6°	6481.5
7°	6207.8
8°	5900.7
9°	5554.3
10°	5157.5
11°	4697.6
12°	4169.8
13°	3591.6
14°	2986.9
15°	2416.2
16°	1911.2
17°	1489.0
18°	1171.2
19°	936.8
20°	775.0
21°	647.7
22°	543.7
23°	454.1
24°	379.8
25°	315.1
27.5°	186.7
30°	116.7
32.5°	74.8
35°	47.7
37.5°	28.6
40°	14.9
42.5°	9.5
45°	6.4
47.5°	3.7
50°	2.1
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0



TEST NUMBER: P1299775
CATALOG NUMBER: P3A17R25W2N902750DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)