

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299963

Luminaire Tested: P3A17R25W2N902765DE010 E3D1WMH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R25W2N902765DE010 E3D1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1638.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299963

CATALOG NUMBER: P3A17R25W2N902765DE010 E3D1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299963

CATALOG NUMBER: P3A17R25W2N902765DE010 E3D1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99		97			
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96		94			
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93		92			
4	106	101	97	94		104	100	96	94		98	95	92		96	93	91		94	92	90		89			
5	103	97	93	91		101	96	93	90		95	92	90		93	91	89		92	90	88		87			
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86		85			
7	98	92	88	85		97	91	87	85		90	87	84		89	86	84		88	86	84		83			
8	95	89	85	83		94	89	85	83		88	85	82		87	84	82		86	84	82		81			
9	93	87	83	81		92	86	83	80		86	83	80		85	82	80		84	82	80		79			
10	91	85	81	79		90	84	81	79		84	81	78		83	80	78		83	80	78		77			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1793913
5°	1661805
10°	1285748
15°	614124
20°	202481
25°	85360
30°	33094
35°	14322
40°	4752
45°	2202
50°	819
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2202 cd/sqm

TEST NUMBER: P1299963

CATALOG NUMBER: P3A17R25W2N902765DE010 E3D1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	663.6	40.5
10°-20°	754.8	46.1
20°-30°	175.4	10.7
30°-40°	36.8	2.2
40°-50°	6.0	0.4
50°-60°	1.0	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.8	97.3
0°-40°	1630.6	99.5
0°-60°	1637.5	100.0
0°-90°	1638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8181	
5°	7550	664
15°	2705	755
25°	353	175
35°	54	37
45°	7	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1299963

CATALOG NUMBER: P3A17R25W2N902765DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	8180.9
1°	8164.3
2°	8079.4
3°	7960.0
4°	7777.7
5°	7549.6
6°	7256.8
7°	6950.4
8°	6606.5
9°	6218.7
10°	5774.4
11°	5259.5
12°	4668.6
13°	4021.3
14°	3344.2
15°	2705.2
16°	2139.8
17°	1667.1
18°	1311.3
19°	1048.8
20°	867.7
21°	725.1
22°	608.7
23°	508.4
24°	425.2
25°	352.8
27.5°	209.1
30°	130.7
32.5°	83.7
35°	53.5
37.5°	32.1
40°	16.6
42.5°	10.7
45°	7.1
47.5°	4.2
50°	2.4
52.5°	1.2
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0



TEST NUMBER: P1299963

CATALOG NUMBER: P3A17R25W2N902765DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)