

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290233

Luminaire Tested: P3A05R50W2N902765DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R50W2N902765DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 346.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290233
CATALOG NUMBER: P3A05R50W2N902765DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290233

CATALOG NUMBER: P3A05R50W2N902765DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70323
5°	69271
10°	66220
15°	61317
20°	55095
25°	48438
30°	41196
35°	33408
40°	25104
45°	16157
50°	7676
55°	6040
60°	5701
65°	5344
70°	4809
75°	4321
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16157 cd/sqm



TEST NUMBER: P1290233

CATALOG NUMBER: P3A05R50W2N902765DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	8.5
10°-20°	75.3	21.8
20°-30°	91.5	26.4
30°-40°	77.6	22.4
40°-50°	40.3	11.7
50°-60°	14.5	4.2
60°-70°	10.1	2.9
70°-80°	5.4	1.6
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.3	56.7
0°-40°	273.9	79.2
0°-60°	328.8	95.0
0°-90°	346.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	346.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	321	
5°	315	30
15°	270	75
25°	200	92
35°	125	78
45°	52	40
55°	16	15
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1290233
CATALOG NUMBER: P3A05R50W2N902765DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	320.7
2.5°	319.5
5°	314.7
7.5°	307.6
10°	297.4
12.5°	284.3
15°	270.1
17.5°	253.9
20°	236.1
22.5°	218.0
25°	200.2
27.5°	181.7
30°	162.7
32.5°	143.7
35°	124.8
37.5°	106.2
40°	87.7
42.5°	69.9
45°	52.1
47.5°	34.8
50°	22.5
52.5°	17.4
55°	15.8
57.5°	14.2
60°	13.0
62.5°	11.5
65°	10.3
67.5°	8.7
70°	7.5
72.5°	6.3
75°	5.1
77.5°	3.9
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)