

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300148

Luminaire Tested: P3A17R30W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R30W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 620.1 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300148

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1300148

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90		
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86		
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82		
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78		
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75		
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71		
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69		
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361791
5°	344353
10°	289641
15°	208877
20°	129558
25°	73698
30°	40943
35°	22272
40°	11736
45°	6357
50°	3411
55°	2256
60°	2061
65°	2127
70°	1859
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6357 cd/sqm

TEST NUMBER: P1300148

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.9	22.7
10°-20°	250.4	40.4
20°-30°	144.7	23.3
30°-40°	54.9	8.9
40°-50°	16.9	2.7
50°-60°	5.7	0.9
60°-70°	3.8	0.6
70°-80°	2.1	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.0	86.4
0°-40°	590.9	95.3
0°-60°	613.5	98.9
0°-90°	620.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1650	
5°	1564	141
15°	920	250
25°	305	145
35°	83	55
45°	20	17
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1300148

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1649.9
1°	1648.7
2°	1638.8
3°	1620.0
4°	1596.6
5°	1564.4
6°	1523.4
7°	1477.7
8°	1426.7
9°	1365.8
10°	1300.8
11°	1230.5
12°	1156.2
13°	1078.3
14°	999.2
15°	920.1
17.5°	725.7
20°	555.2
22.5°	411.7
25°	304.6
27.5°	221.4
30°	161.7
32.5°	116.6
35°	83.2
37.5°	58.0
40°	41.0
42.5°	28.7
45°	20.5
47.5°	14.1
50°	10.0
52.5°	7.0
55°	5.9
57.5°	5.3
60°	4.7
62.5°	4.1
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.3
75°	1.8
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0



TEST NUMBER: P1300148

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)