

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300181

Luminaire Tested: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300181  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 481.0 lumens  
Efficiency: N/A  
Efficacy: 24.8 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300181  
CATALOG NUMBER: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300181

CATALOG NUMBER: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.8	9.7
10°-20°	112.6	23.4
20°-30°	126.9	26.4
30°-40°	101.3	21.1
40°-50°	52.1	10.8
50°-60°	19.6	4.1
60°-70°	12.8	2.7
70°-80°	6.9	1.4
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.3	59.5
0°-40°	387.6	80.6
0°-60°	459.2	95.5
0°-90°	481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	481.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	518	
5°	505	47
15°	405	113
25°	277	127
35°	163	101
45°	66	52
55°	20	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1300181  
CATALOG NUMBER: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	518.2
1°	518.2
2°	516.5
3°	513.5
4°	509.4
5°	504.7
6°	498.7
7°	491.1
8°	482.8
9°	473.4
10°	463.9
11°	453.3
12°	442.1
13°	430.3
14°	417.9
15°	404.9
17.5°	371.8
20°	338.8
22.5°	306.9
25°	276.8
27.5°	247.3
30°	219.6
32.5°	191.2
35°	162.9
37.5°	135.2
40°	109.2
42.5°	86.2
45°	66.1
47.5°	49.0
50°	34.2
52.5°	24.2
55°	20.1
57.5°	18.3
60°	16.5
62.5°	14.8
65°	13.0
67.5°	11.2
70°	9.4
72.5°	7.7
75°	6.5
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	0.6



TEST NUMBER: P1300181  
CATALOG NUMBER: P3A17R30W2N902750DE010 E3DLD1GPH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)