

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300277

Luminaire Tested: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1300277  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R30W2N902765DE010 E3CD1MMS\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1520.0 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300277

CATALOG NUMBER: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1300277

CATALOG NUMBER: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 | 99  | 98  | 97  |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  |  | 100 | 99  | 97  |  | 98  | 96  | 95  | 94  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 95  | 94  | 92  | 91  |
| 4   | 105 | 100 | 96  | 93  | 103 | 99  | 95  | 92  | 97  | 94  | 91  |  | 95  | 92  | 90  |  | 93  | 91  | 89  | 88  |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 91  | 88  | 87  | 85  |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 88  | 85  |  | 90  | 87  | 85  |  | 89  | 86  | 84  | 83  |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  |  | 87  | 84  | 82  |  | 86  | 84  | 82  | 81  |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  |  | 85  | 82  | 80  |  | 84  | 82  | 80  | 79  |
| 9   | 91  | 85  | 81  | 78  | 90  | 84  | 81  | 78  | 84  | 80  | 78  |  | 83  | 80  | 78  |  | 82  | 79  | 77  | 77  |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 78  | 76  | 82  | 78  | 76  |  | 81  | 78  | 76  |  | 80  | 77  | 75  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1237796 |
| 5°  | 1214393 |
| 10° | 1075064 |
| 15° | 681116  |
| 20° | 258532  |
| 25° | 76553   |
| 30° | 30232   |
| 35° | 9262    |
| 40° | 4093    |
| 45° | 1489    |
| 50° | 1228    |
| 55° | 918     |
| 60° | 1053    |
| 65° | 1245    |
| 70° | 769     |
| 75° | 1017    |
| 80° | 1515    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1515 cd/sqm

TEST NUMBER: P1300277

CATALOG NUMBER: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 507.2  | 33.4      |
| 10°-20°   | 790.4  | 52.0      |
| 20°-30°   | 183.5  | 12.1      |
| 30°-40°   | 28.4   | 1.9       |
| 40°-50°   | 4.9    | 0.3       |
| 50°-60°   | 2.3    | 0.2       |
| 60°-70°   | 1.9    | 0.1       |
| 70°-80°   | 1.3    | 0.1       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1481.1 | 97.4      |
| 0°-40°    | 1509.5 | 99.3      |
| 0°-60°    | 1516.7 | 99.8      |
| 0°-90°    | 1520.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1520.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5645 |      |
| 5°  | 5517 | 507  |
| 15° | 3000 | 790  |
| 25° | 316  | 184  |
| 35° | 35   | 28   |
| 45° | 5    | 5    |
| 55° | 2    | 2    |
| 65° | 2    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1300277

CATALOG NUMBER: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5644.8 |
| 1°    | 5641.2 |
| 2°    | 5625.7 |
| 3°    | 5599.4 |
| 4°    | 5566.0 |
| 5°    | 5517.0 |
| 6°    | 5456.1 |
| 7°    | 5365.4 |
| 8°    | 5241.2 |
| 9°    | 5058.6 |
| 10°   | 4828.2 |
| 11°   | 4530.9 |
| 12°   | 4195.4 |
| 13°   | 3822.9 |
| 14°   | 3413.4 |
| 15°   | 3000.3 |
| 17.5° | 1962.8 |
| 20°   | 1107.9 |
| 22.5° | 565.9  |
| 25°   | 316.4  |
| 27.5° | 194.6  |
| 30°   | 119.4  |
| 32.5° | 64.5   |
| 35°   | 34.6   |
| 37.5° | 22.7   |
| 40°   | 14.3   |
| 42.5° | 8.4    |
| 45°   | 4.8    |
| 47.5° | 3.6    |
| 50°   | 3.6    |
| 52.5° | 2.4    |
| 55°   | 2.4    |
| 57.5° | 2.4    |
| 60°   | 2.4    |
| 62.5° | 2.4    |
| 65°   | 2.4    |
| 67.5° | 1.2    |
| 70°   | 1.2    |
| 72.5° | 1.2    |
| 75°   | 1.2    |
| 77.5° | 1.2    |
| 80°   | 1.2    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1300277

CATALOG NUMBER: P3A17R30W2N902765DE010 E3CD1MMS\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)