

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300437

Luminaire Tested: P3A17R30W2N902765DE010 E3PHLD1MW_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R30W2N902765DE010 E3PHLD1MW_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 937.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300437
CATALOG NUMBER: P3A17R30W2N902765DE010 E3PHLD1MW_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300437

CATALOG NUMBER: P3A17R30W2N902765DE010 E3PHLD1MW_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230881
5°	220691
10°	190355
15°	157776
20°	129348
25°	104256
30°	84038
35°	68850
40°	57193
45°	48501
50°	41483
55°	35860
60°	32015
65°	27967
70°	24491
75°	20588
80°	15406
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48501 cd/sqm



TEST NUMBER: P1300437

CATALOG NUMBER: P3A17R30W2N902765DE010 E3PHLD1MW_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	9.7
10°-20°	193.8	20.7
20°-30°	198.7	21.2
30°-40°	162.4	17.3
40°-50°	121.5	13.0
50°-60°	85.3	9.1
60°-70°	53.7	5.7
70°-80°	25.9	2.8
80°-90°	5.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.4	51.6
0°-40°	645.7	68.9
0°-60°	852.5	91.0
0°-90°	937.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1053	
5°	1003	91
15°	695	194
25°	431	199
35°	257	162
45°	156	121
55°	94	85
65°	54	54
75°	24	26
85°	4	5
90°	0	



TEST NUMBER: P1300437
CATALOG NUMBER: P3A17R30W2N902765DE010 E3PHLD1MW_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1052.9
2.5°	1042.5
5°	1002.6
7.5°	936.5
10°	854.9
12.5°	774.9
15°	695.0
17.5°	622.0
20°	554.3
22.5°	490.0
25°	430.9
27.5°	378.8
30°	331.9
32.5°	293.6
35°	257.2
37.5°	227.6
40°	199.8
42.5°	177.2
45°	156.4
47.5°	137.3
50°	121.6
52.5°	107.7
55°	93.8
57.5°	83.4
60°	73.0
62.5°	62.6
65°	53.9
67.5°	45.2
70°	38.2
72.5°	31.3
75°	24.3
77.5°	17.4
80°	12.2
82.5°	7.0
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)