

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300684

Luminaire Tested: P3A17R35W2N902765DE010 E3DLD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R35W2N902765DE010 E3DLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 975.0 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300684

CATALOG NUMBER: P3A17R35W2N902765DE010 E3DLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300684

CATALOG NUMBER: P3A17R35W2N902765DE010 E3DLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96	94	93		91			
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89	87	85		83			
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	78		76			
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71		69			
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66		64			
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68	64	61		59			
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64	60	56		55			
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61	56	52		51			
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49		48			
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54	49	46		45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222723
5°	218005
10°	204160
15°	183247
20°	159404
25°	135855
30°	113790
35°	90641
40°	65523
45°	41462
50°	22618
55°	15674
60°	14780
65°	13750
70°	13143
75°	11268
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41462 cd/sqm

TEST NUMBER: P1300684

CATALOG NUMBER: P3A17R35W2N902765DE010 E3DLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	9.5
10°-20°	224.6	23.0
20°-30°	257.4	26.4
30°-40°	210.1	21.5
40°-50°	105.9	10.9
50°-60°	39.4	4.0
60°-70°	26.4	2.7
70°-80°	14.6	1.5
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	58.9
0°-40°	784.3	80.4
0°-60°	929.6	95.3
0°-90°	975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1016	
5°	990	92
15°	807	225
25°	562	257
35°	339	210
45°	134	106
55°	41	39
65°	26	26
75°	13	15
85°	4	4
90°	0	

TEST NUMBER: P1300684

CATALOG NUMBER: P3A17R35W2N902765DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1015.7
1°	1014.5
2°	1012.1
3°	1007.2
4°	1000.0
5°	990.4
6°	978.3
7°	966.3
8°	950.6
9°	935.0
10°	916.9
11°	897.6
12°	877.1
13°	854.2
14°	830.1
15°	807.2
17.5°	745.8
20°	683.1
22.5°	619.3
25°	561.5
27.5°	504.8
30°	449.4
32.5°	394.0
35°	338.6
37.5°	283.1
40°	228.9
42.5°	178.3
45°	133.7
47.5°	96.4
50°	66.3
52.5°	48.2
55°	41.0
57.5°	37.4
60°	33.7
62.5°	30.1
65°	26.5
67.5°	22.9
70°	20.5
72.5°	16.9
75°	13.3
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4



TEST NUMBER: P1300684

CATALOG NUMBER: P3A17R35W2N902765DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)