

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290640

Luminaire Tested: P3A05R60W2N902750DE010 E3D1MW\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290640  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R60W2N902750DE010 E3D1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 511.0 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290640

CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1290640

CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  |  | 90  | 87  | 84  |  | 88  |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 79  |
| 6   | 88  | 79  | 73  | 69  | 87  | 78  | 73  | 69  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 122030 |
| 5°  | 117191 |
| 10° | 120661 |
| 15° | 122203 |
| 20° | 107903 |
| 25° | 90949  |
| 30° | 73758  |
| 35° | 48024  |
| 40° | 22070  |
| 45° | 8466   |
| 50° | 2831   |
| 55° | 765    |
| 60° | 702    |
| 65° | 623    |
| 70° | 513    |
| 75° | 678    |
| 80° | 505    |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8466 cd/sqm

TEST NUMBER: P1290640

CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1MW\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 51.2   | 10.0      |
| 10°-20°   | 147.4  | 28.8      |
| 20°-30°   | 171.9  | 33.6      |
| 30°-40°   | 110.9  | 21.7      |
| 40°-50°   | 24.9   | 4.9       |
| 50°-60°   | 2.5    | 0.5       |
| 60°-70°   | 1.2    | 0.2       |
| 70°-80°   | 0.7    | 0.1       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 370.6  | 72.5      |
| 0°-40°    | 481.5  | 94.2      |
| 0°-60°    | 508.9  | 99.6      |
| 0°-90°    | 511.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 511.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 556 |      |
| 5°  | 532 | 51   |
| 15° | 538 | 147  |
| 25° | 376 | 172  |
| 35° | 179 | 111  |
| 45° | 27  | 25   |
| 55° | 2   | 3    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1290640

CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 556.5 |
| 2.5°  | 547.4 |
| 5°    | 532.4 |
| 7.5°  | 531.6 |
| 10°   | 541.9 |
| 12.5° | 548.6 |
| 15°   | 538.3 |
| 17.5° | 507.5 |
| 20°   | 462.4 |
| 22.5° | 415.4 |
| 25°   | 375.9 |
| 27.5° | 337.1 |
| 30°   | 291.3 |
| 32.5° | 237.5 |
| 35°   | 179.4 |
| 37.5° | 122.5 |
| 40°   | 77.1  |
| 42.5° | 46.2  |
| 45°   | 27.3  |
| 47.5° | 15.8  |
| 50°   | 8.3   |
| 52.5° | 2.8   |
| 55°   | 2.0   |
| 57.5° | 1.6   |
| 60°   | 1.6   |
| 62.5° | 1.2   |
| 65°   | 1.2   |
| 67.5° | 1.2   |
| 70°   | 0.8   |
| 72.5° | 0.8   |
| 75°   | 0.8   |
| 77.5° | 0.4   |
| 80°   | 0.4   |
| 82.5° | 0.4   |
| 85°   | 0.4   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)