

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300807

Luminaire Tested: P3A17R40W2N902750DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1300807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R40W2N902750DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 618.0 lumens  
Efficiency: N/A  
Efficacy: 31.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300807

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot



CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1GPH\_2700K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 114 | 111 | 109 | 107 |  | 112 | 109 | 107 | 105 |  | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |  | 94  |  |  |   |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 92  | 91  |  | 89  |  |  |   |
| 3   | 104 | 99  | 94  | 91  |  | 102 | 97  | 93  | 90  |  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |  | 84  |  |  |   |
| 4   | 100 | 93  | 88  | 85  |  | 98  | 92  | 88  | 84  |  | 90  | 86  | 83  |  | 88  | 85  | 82  |  | 86  | 84  | 81  |  | 80  |  |  |   |
| 5   | 96  | 88  | 83  | 79  |  | 94  | 88  | 83  | 79  |  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |  | 76  |  |  |   |
| 6   | 92  | 84  | 79  | 75  |  | 91  | 83  | 78  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |  | 72  |  |  |   |
| 7   | 88  | 80  | 75  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |  | 69  |  |  |   |
| 8   | 85  | 76  | 71  | 68  |  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 67  |  | 65  |  |  |   |
| 9   | 82  | 73  | 68  | 64  |  | 81  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 70  | 66  | 64  |  | 63  |  |  |   |
| 10  | 78  | 70  | 65  | 62  |  | 78  | 70  | 65  | 61  |  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 64  | 61  |  | 60  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 273465 |
| 5°  | 265507 |
| 10° | 240944 |
| 15° | 199048 |
| 20° | 143582 |
| 25° | 88820  |
| 30° | 48083  |
| 35° | 24842  |
| 40° | 13511  |
| 45° | 7567   |
| 50° | 3787   |
| 55° | 2829   |
| 60° | 2544   |
| 65° | 2491   |
| 70° | 2372   |
| 75° | 2288   |
| 80° | 2020   |
| 85° | 1258   |

**MAXIMUM LUMINANCE 45°-90°:**

Luminance: 7567 cd/sqm

TEST NUMBER: P1300807

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 111.2  | 18.0      |
| 10°-20°   | 238.8  | 38.6      |
| 20°-30°   | 170.4  | 27.6      |
| 30°-40°   | 62.7   | 10.1      |
| 40°-50°   | 19.7   | 3.2       |
| 50°-60°   | 6.9    | 1.1       |
| 60°-70°   | 4.7    | 0.8       |
| 70°-80°   | 2.8    | 0.5       |
| 80°-90°   | 0.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 520.3  | 84.2      |
| 0°-40°    | 583.1  | 94.4      |
| 0°-60°    | 609.6  | 98.7      |
| 0°-90°    | 618.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 618.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1247 |      |
| 5°  | 1206 | 111  |
| 15° | 877  | 239  |
| 25° | 367  | 170  |
| 35° | 93   | 63   |
| 45° | 24   | 20   |
| 55° | 7    | 7    |
| 65° | 5    | 5    |
| 75° | 3    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1300807

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1247.1 |
| 2.5°  | 1237.5 |
| 5°    | 1206.2 |
| 7.5°  | 1154.3 |
| 10°   | 1082.1 |
| 12.5° | 990.3  |
| 15°   | 876.8  |
| 17.5° | 749.5  |
| 20°   | 615.3  |
| 22.5° | 483.2  |
| 25°   | 367.1  |
| 27.5° | 269.5  |
| 30°   | 189.9  |
| 32.5° | 133.1  |
| 35°   | 92.8   |
| 37.5° | 65.8   |
| 40°   | 47.2   |
| 42.5° | 33.9   |
| 45°   | 24.4   |
| 47.5° | 16.4   |
| 50°   | 11.1   |
| 52.5° | 8.0    |
| 55°   | 7.4    |
| 57.5° | 6.9    |
| 60°   | 5.8    |
| 62.5° | 5.3    |
| 65°   | 4.8    |
| 67.5° | 4.2    |
| 70°   | 3.7    |
| 72.5° | 3.2    |
| 75°   | 2.7    |
| 77.5° | 2.1    |
| 80°   | 1.6    |
| 82.5° | 1.1    |
| 85°   | 0.5    |
| 87.5° | 0.5    |
| 90°   | 0.0    |

(END OF REPORT)