

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300820

Luminaire Tested: P3A17R40W2N902750DE010 E3DL1LI\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1300820  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R40W2N902750DE010 E3DL1LI\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1412.0 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300820

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1LI\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1300820

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1LI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 94  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 92  | 91  | 91  | 91  | 89  |
| 3   | 104 | 99  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 91  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 86  | 86  | 84  |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  | 90  | 86  | 83  | 88  | 85  | 82  | 86  | 84  | 81  | 81  | 81  | 80  |
| 5   | 96  | 88  | 83  | 79  | 94  | 88  | 83  | 79  | 86  | 82  | 78  | 84  | 81  | 78  | 83  | 80  | 77  | 77  | 77  | 76  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 78  | 75  | 82  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 73  | 73  | 72  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 70  | 70  | 69  |
| 8   | 85  | 76  | 71  | 68  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 67  | 67  | 65  |
| 9   | 82  | 73  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 64  | 64  | 64  | 63  |
| 10  | 78  | 70  | 65  | 62  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 64  | 61  | 61  | 61  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 624796 |
| 5°  | 606646 |
| 10° | 550513 |
| 15° | 454804 |
| 20° | 328072 |
| 25° | 202923 |
| 30° | 109865 |
| 35° | 56778  |
| 40° | 30886  |
| 45° | 17304  |
| 50° | 8699   |
| 55° | 6499   |
| 60° | 5833   |
| 65° | 5656   |
| 70° | 5450   |
| 75° | 5168   |
| 80° | 4546   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 17304 cd/sqm

TEST NUMBER: P1300820

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1LI\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 254.0  | 18.0      |
| 10°-20°   | 545.5  | 38.6      |
| 20°-30°   | 389.3  | 27.6      |
| 30°-40°   | 143.3  | 10.2      |
| 40°-50°   | 45.2   | 3.2       |
| 50°-60°   | 15.7   | 1.1       |
| 60°-70°   | 10.8   | 0.8       |
| 70°-80°   | 6.4    | 0.5       |
| 80°-90°   | 1.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1188.9 | 84.2      |
| 0°-40°    | 1332.2 | 94.3      |
| 0°-60°    | 1393.1 | 98.7      |
| 0°-90°    | 1412.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1412.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2849 |      |
| 5°  | 2756 | 254  |
| 15° | 2003 | 546  |
| 25° | 839  | 389  |
| 35° | 212  | 143  |
| 45° | 56   | 45   |
| 55° | 17   | 16   |
| 65° | 11   | 11   |
| 75° | 6    | 6    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1300820

CATALOG NUMBER: P3A17R40W2N902750DE010 E3DL1LI\_4000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2849.3 |
| 2.5°  | 2827.5 |
| 5°    | 2756.0 |
| 7.5°  | 2637.2 |
| 10°   | 2472.4 |
| 12.5° | 2262.7 |
| 15°   | 2003.4 |
| 17.5° | 1712.5 |
| 20°   | 1405.9 |
| 22.5° | 1104.1 |
| 25°   | 838.7  |
| 27.5° | 615.7  |
| 30°   | 433.9  |
| 32.5° | 304.2  |
| 35°   | 212.1  |
| 37.5° | 150.3  |
| 40°   | 107.9  |
| 42.5° | 77.6   |
| 45°   | 55.8   |
| 47.5° | 37.6   |
| 50°   | 25.5   |
| 52.5° | 18.2   |
| 55°   | 17.0   |
| 57.5° | 15.8   |
| 60°   | 13.3   |
| 62.5° | 12.1   |
| 65°   | 10.9   |
| 67.5° | 9.7    |
| 70°   | 8.5    |
| 72.5° | 7.3    |
| 75°   | 6.1    |
| 77.5° | 4.8    |
| 80°   | 3.6    |
| 82.5° | 2.4    |
| 85°   | 1.2    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)