

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290739

Luminaire Tested: P3A05R60W2N902750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 261.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290739

CATALOG NUMBER: P3A05R60W2N902750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290739

CATALOG NUMBER: P3A05R60W2N902750DE010 E3DLP1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94		92			
2	107	101	97	93		104	100	96	92		96	93	90		93	91	88		91	88	86		85			
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	79		78			
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	73		72			
5	90	81	75	70		88	80	74	70		78	73	69		77	72	69		75	71	68		66			
6	85	76	69	65		84	75	69	65		73	68	64		72	67	64		71	66	63		62			
7	81	71	65	60		79	70	64	60		69	64	60		68	63	59		67	62	59		57			
8	77	67	60	56		75	66	60	56		65	60	56		64	59	55		63	58	55		54			
9	73	63	57	52		72	62	56	52		61	56	52		60	55	52		60	55	52		50			
10	69	59	53	49		68	59	53	49		58	53	49		57	52	49		56	52	49		47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66135
5°	64671
10°	60542
15°	54302
20°	46694
25°	38615
30°	30511
35°	22647
40°	15601
45°	9799
50°	5390
55°	3135
60°	2851
65°	2439
70°	2052
75°	2118
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9799 cd/sqm

TEST NUMBER: P1290739

CATALOG NUMBER: P3A05R60W2N902750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	10.5
10°-20°	66.4	25.5
20°-30°	72.9	27.9
30°-40°	53.1	20.3
40°-50°	25.1	9.6
50°-60°	8.2	3.1
60°-70°	4.7	1.8
70°-80°	2.5	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	166.7	63.8
0°-40°	219.7	84.2
0°-60°	253.1	97.0
0°-90°	261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	302	
5°	294	27
15°	239	66
25°	160	73
35°	85	53
45°	32	25
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1290739

CATALOG NUMBER: P3A05R60W2N902750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	301.6
2.5°	299.9
5°	293.8
7.5°	284.4
10°	271.9
12.5°	256.8
15°	239.2
17.5°	220.2
20°	200.1
22.5°	179.7
25°	159.6
27.5°	139.5
30°	120.5
32.5°	102.2
35°	84.6
37.5°	68.9
40°	54.5
42.5°	42.0
45°	31.6
47.5°	23.0
50°	15.8
52.5°	10.4
55°	8.2
57.5°	7.2
60°	6.5
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.2
72.5°	2.9
75°	2.5
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)