

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300965

Luminaire Tested: P3A17R40W2N902765DE010 E3DL1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R40W2N902765DE010 E3DL1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 692.0 lumens
Efficiency: N/A
Efficacy: 35.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300965
CATALOG NUMBER: P3A17R40W2N902765DE010 E3DL1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300965

CATALOG NUMBER: P3A17R40W2N902765DE010 E3DL1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	18.0
10°-20°	267.4	38.6
20°-30°	190.8	27.6
30°-40°	70.2	10.2
40°-50°	22.1	3.2
50°-60°	7.7	1.1
60°-70°	5.3	0.8
70°-80°	3.2	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.6	84.2
0°-40°	652.9	94.3
0°-60°	682.7	98.6
0°-90°	692.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	692.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1351	125
15°	982	267
25°	411	191
35°	104	70
45°	27	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1300965
CATALOG NUMBER: P3A17R40W2N902765DE010 E3DL1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1396.4
2.5°	1385.7
5°	1350.7
7.5°	1292.5
10°	1211.7
12.5°	1108.9
15°	981.8
17.5°	839.3
20°	689.0
22.5°	541.1
25°	411.0
27.5°	301.7
30°	212.6
32.5°	149.1
35°	103.9
37.5°	73.7
40°	52.9
42.5°	38.0
45°	27.3
47.5°	18.4
50°	12.5
52.5°	8.9
55°	8.3
57.5°	7.7
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.8
70°	4.2
72.5°	3.6
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)