

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290787

Luminaire Tested: P3A05R60W2N902765DE010 E3D1LI_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3D1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290787

CATALOG NUMBER: P3A05R60W2N902765DE010 E3D1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290787

CATALOG NUMBER: P3A05R60W2N902765DE010 E3D1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124201
5°	117235
10°	114204
15°	111578
20°	103749
25°	92739
30°	70846
35°	40903
40°	15887
45°	6605
50°	1467
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6605 cd/sqm

TEST NUMBER: P1290787

CATALOG NUMBER: P3A05R60W2N902765DE010 E3D1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	10.6
10°-20°	136.9	28.9
20°-30°	171.5	36.2
30°-40°	95.9	20.2
40°-50°	18.2	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.7	75.7
0°-40°	454.6	95.9
0°-60°	473.7	99.9
0°-90°	474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	566	
5°	533	50
15°	492	137
25°	383	171
35°	153	96
45°	21	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1290787

CATALOG NUMBER: P3A05R60W2N902765DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	566.4
1°	564.0
2°	556.7
3°	548.0
4°	539.8
5°	532.6
6°	527.2
7°	522.6
8°	519.1
9°	515.8
10°	512.9
11°	509.9
12°	506.7
13°	502.6
14°	497.7
15°	491.5
16°	484.0
17°	475.4
18°	465.7
19°	454.7
20°	444.6
21°	433.7
22°	422.5
23°	410.7
24°	397.7
25°	383.3
26°	366.5
27°	347.7
28°	326.5
29°	304.0
30°	279.8
31°	255.4
32°	230.2
32.5°	216.4
33°	204.0
34°	178.2
35°	152.8
36°	129.9
37°	105.7
37.5°	94.6
38°	83.8
39°	67.5
40°	55.5
42.5°	33.7
45°	21.3



TEST NUMBER: P1290787

CATALOG NUMBER: P3A05R60W2N902765DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.8
50°	4.3
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)