

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301242

Luminaire Tested: P3A17R45W2N902765DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R45W2N902765DE010 E3DL1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 34.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301242

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1301242

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94											94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88											88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83											83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78											78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74											74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70											70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66											66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62											62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59											59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57											57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247853
5°	242042
10°	222508
15°	188537
20°	146266
25°	102248
30°	64415
35°	37932
40°	21469
45°	10420
50°	3616
55°	2944
60°	2851
65°	2750
70°	2629
75°	2542
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10420 cd/sqm

TEST NUMBER: P1301242

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.8	15.4
10°-20°	228.1	34.6
20°-30°	193.7	29.3
30°-40°	92.4	14.0
40°-50°	27.8	4.2
50°-60°	7.1	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.5	79.3
0°-40°	615.9	93.3
0°-60°	650.8	98.6
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1130	
5°	1100	102
15°	830	228
25°	423	194
35°	142	92
45°	34	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1301242

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1130.3
2.5°	1123.2
5°	1099.6
7.5°	1058.9
10°	999.3
12.5°	920.2
15°	830.5
17.5°	730.7
20°	626.8
22.5°	521.2
25°	422.6
27.5°	332.9
30°	254.4
32.5°	191.2
35°	141.7
37.5°	104.5
40°	75.0
42.5°	51.9
45°	33.6
47.5°	18.9
50°	10.6
52.5°	8.3
55°	7.7
57.5°	7.1
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)