

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301276

Luminaire Tested: P3A17R45W2N902765DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R45W2N902765DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 515.0 lumens
Efficiency: N/A
Efficacy: 26.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301276
CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301276

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	8.8
10°-20°	113.5	22.0
20°-30°	134.9	26.2
30°-40°	117.2	22.8
40°-50°	58.8	11.4
50°-60°	20.4	4.0
60°-70°	14.3	2.8
70°-80°	8.0	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.9	57.1
0°-40°	411.1	79.8
0°-60°	490.3	95.2
0°-90°	515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	498	
5°	487	46
15°	408	114
25°	294	135
35°	190	117
45°	75	59
55°	22	20
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1301276
CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	498.0
2.5°	495.6
5°	487.3
7.5°	474.2
10°	455.8
12.5°	433.3
15°	407.7
17.5°	379.3
20°	350.8
22.5°	321.7
25°	293.8
27.5°	267.1
30°	241.0
32.5°	216.0
35°	189.9
37.5°	162.0
40°	132.4
42.5°	103.3
45°	74.8
47.5°	49.3
50°	31.5
52.5°	24.3
55°	22.0
57.5°	20.2
60°	18.4
62.5°	16.6
65°	14.2
67.5°	12.5
70°	10.7
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.6
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)