

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301424

Luminaire Tested: P3A17R50W2N902750DE010 E3DL1WH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1301424  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R50W2N902750DE010 E3DL1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 895.0 lumens  
Efficiency: N/A  
Efficacy: 46.1 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301424

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DL1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1301424

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DL1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 95  | 94  |  | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  |  | 85  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  | 83  | 81  |  | 79  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 75  |  | 73  |
| 5   | 91  | 83  | 76  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 77  | 73  | 70  |  | 68  |
| 6   | 87  | 77  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 72  | 68  | 65  |  | 64  |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 68  | 64  | 61  |  | 60  |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  | 61  | 57  |  | 56  |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 55  |  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 53  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  | 54  | 51  |  | 50  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 260308 |
| 5°  | 253312 |
| 10° | 233574 |
| 15° | 205427 |
| 20° | 171865 |
| 25° | 136290 |
| 30° | 99990  |
| 35° | 68743  |
| 40° | 43682  |
| 45° | 24406  |
| 50° | 13236  |
| 55° | 11125  |
| 60° | 9561   |
| 65° | 8821   |
| 70° | 7758   |
| 75° | 7202   |
| 80° | 6061   |
| 85° | 6038   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24406 cd/sqm

TEST NUMBER: P1301424

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DL1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 106.6  | 11.9      |
| 10°-20°   | 250.6  | 28.0      |
| 20°-30°   | 256.3  | 28.6      |
| 30°-40°   | 162.5  | 18.2      |
| 40°-50°   | 64.7   | 7.2       |
| 50°-60°   | 26.2   | 2.9       |
| 60°-70°   | 16.8   | 1.9       |
| 70°-80°   | 8.6    | 1.0       |
| 80°-90°   | 2.6    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 613.6  | 68.6      |
| 0°-40°    | 776.1  | 86.7      |
| 0°-60°    | 867.0  | 96.9      |
| 0°-90°    | 895.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 895.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1187 |      |
| 5°  | 1151 | 107  |
| 15° | 905  | 251  |
| 25° | 563  | 256  |
| 35° | 257  | 163  |
| 45° | 79   | 65   |
| 55° | 29   | 26   |
| 65° | 17   | 17   |
| 75° | 8    | 9    |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1301424

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DL1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1187.1 |
| 2.5°  | 1178.6 |
| 5°    | 1150.8 |
| 7.5°  | 1107.2 |
| 10°   | 1049.0 |
| 12.5° | 980.0  |
| 15°   | 904.9  |
| 17.5° | 822.5  |
| 20°   | 736.5  |
| 22.5° | 650.5  |
| 25°   | 563.3  |
| 27.5° | 476.1  |
| 30°   | 394.9  |
| 32.5° | 322.2  |
| 35°   | 256.8  |
| 37.5° | 201.1  |
| 40°   | 152.6  |
| 42.5° | 112.7  |
| 45°   | 78.7   |
| 47.5° | 53.3   |
| 50°   | 38.8   |
| 52.5° | 32.7   |
| 55°   | 29.1   |
| 57.5° | 25.4   |
| 60°   | 21.8   |
| 62.5° | 19.4   |
| 65°   | 17.0   |
| 67.5° | 14.5   |
| 70°   | 12.1   |
| 72.5° | 9.7    |
| 75°   | 8.5    |
| 77.5° | 6.1    |
| 80°   | 4.8    |
| 82.5° | 3.6    |
| 85°   | 2.4    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)