

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291834

Luminaire Tested: P3A09R15W2N902765DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R15W2N902765DE010 E3DLP1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 549.0 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291834

CATALOG NUMBER: P3A09R15W2N902765DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1291834

CATALOG NUMBER: P3A09R15W2N902765DE010 E3DLP1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97		95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93		91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88		87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85		83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81		80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78		77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75		74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73		72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70		69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	468998
5°	416310
10°	289106
15°	170966
20°	97378
25°	55673
30°	30790
35°	16410
40°	9074
45°	4931
50°	3070
55°	2409
60°	2105
65°	1920
70°	1667
75°	1779
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4931 cd/sqm

TEST NUMBER: P1291834

CATALOG NUMBER: P3A09R15W2N902765DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	29.3
10°-20°	212.3	38.7
20°-30°	109.3	19.9
30°-40°	41.0	7.5
40°-50°	13.4	2.4
50°-60°	5.8	1.1
60°-70°	3.7	0.7
70°-80°	2.1	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	482.4	87.9
0°-40°	523.4	95.3
0°-60°	542.6	98.8
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2139	
5°	1891	161
15°	753	212
25°	230	109
35°	61	41
45°	16	13
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1291834

CATALOG NUMBER: P3A09R15W2N902765DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2138.8
1°	2134.5
2°	2106.5
3°	2053.1
4°	1982.7
5°	1891.3
6°	1787.6
7°	1673.9
8°	1547.5
9°	1422.7
10°	1298.4
12.5°	999.0
15°	753.1
17.5°	563.8
20°	417.3
22.5°	311.5
25°	230.1
27.5°	167.7
30°	121.6
32.5°	86.2
35°	61.3
37.5°	43.9
40°	31.7
42.5°	22.7
45°	15.9
47.5°	11.6
50°	9.0
52.5°	7.4
55°	6.3
57.5°	5.3
60°	4.8
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)