

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292079

Luminaire Tested: P3A09R20W2N902765DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R20W2N902765DE010 E3DL1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292079

CATALOG NUMBER: P3A09R20W2N902765DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292079

CATALOG NUMBER: P3A09R20W2N902765DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97		95			
2	110	106	102	100		108	104	101	98		101	98	96		98	96	94		95	94	92		91			
3	106	100	96	93		104	99	95	92		97	93	91		94	92	89		92	90	88		87			
4	102	96	91	88		100	95	90	87		92	89	86		91	88	85		89	86	84		83			
5	98	91	87	83		97	90	86	83		89	85	82		87	84	81		86	83	81		79			
6	95	87	83	79		93	87	82	79		85	81	78		84	81	78		83	80	77		76			
7	91	84	79	76		90	83	79	76		82	78	75		81	78	75		80	77	75		73			
8	88	81	76	73		87	80	76	73		79	75	72		78	75	72		78	74	72		71			
9	85	78	73	70		85	77	73	70		77	73	70		76	72	69		75	72	69		68			
10	83	75	71	68		82	75	70	67		74	70	67		73	70	67		73	69	67		66			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	463932
5°	421725
10°	311684
15°	192805
20°	110096
25°	62858
30°	35246
35°	19194
40°	10505
45°	5768
50°	3377
55°	2447
60°	2281
65°	2127
70°	1859
75°	1949
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5768 cd/sqm

TEST NUMBER: P1292079

CATALOG NUMBER: P3A09R20W2N902765DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.9	27.5
10°-20°	236.8	39.3
20°-30°	123.6	20.5
30°-40°	47.8	7.9
40°-50°	15.5	2.6
50°-60°	6.1	1.0
60°-70°	4.0	0.7
70°-80°	2.4	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.4	87.3
0°-40°	574.2	95.2
0°-60°	595.8	98.8
0°-90°	603.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2116	
5°	1916	166
15°	849	237
25°	260	124
35°	72	48
45°	19	16
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1292079

CATALOG NUMBER: P3A09R20W2N902765DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2115.7
1°	2111.7
2°	2086.6
3°	2048.2
4°	1988.7
5°	1915.9
6°	1829.7
7°	1734.2
8°	1623.5
9°	1515.7
10°	1399.8
12.5°	1112.6
15°	849.3
17.5°	635.5
20°	471.8
22.5°	349.5
25°	259.8
27.5°	191.7
30°	139.2
32.5°	100.8
35°	71.7
37.5°	51.8
40°	36.7
42.5°	26.2
45°	18.6
47.5°	13.4
50°	9.9
52.5°	7.6
55°	6.4
57.5°	5.8
60°	5.2
62.5°	4.7
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)