

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287830

Luminaire Tested: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1287830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 316.9 lumens  
Efficiency: N/A  
Efficacy: 53.7 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287830

CATALOG NUMBER: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1287830

CATALOG NUMBER: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 92  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 95  | 91  | 95  | 92  | 89  | 92  | 90  | 87  | 90  | 87  | 85  | 83  |    |    |
| 3   | 100 | 93  | 87  | 83  | 98  | 91  | 86  | 82  | 89  | 84  | 81  | 86  | 82  | 79  | 84  | 81  | 78  | 76  |    |    |
| 4   | 94  | 86  | 80  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 70  |    |    |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  | 75  | 71  | 67  | 74  | 70  | 66  | 65  |    |    |
| 6   | 84  | 74  | 68  | 63  | 83  | 73  | 67  | 63  | 72  | 66  | 62  | 70  | 66  | 62  | 69  | 65  | 61  | 60  |    |    |
| 7   | 80  | 70  | 63  | 58  | 78  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 57  | 56  |    |    |
| 8   | 76  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 53  | 52  |    |    |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 50  | 49  |    |    |
| 10  | 68  | 58  | 52  | 48  | 67  | 57  | 51  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 46  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 79950 |
| 5°  | 77790 |
| 10° | 71096 |
| 15° | 62271 |
| 20° | 53415 |
| 25° | 44591 |
| 30° | 35702 |
| 35° | 26769 |
| 40° | 19436 |
| 45° | 12714 |
| 50° | 7949  |
| 55° | 5390  |
| 60° | 4736  |
| 65° | 4358  |
| 70° | 4103  |
| 75° | 3728  |
| 80° | 3536  |
| 85° | 3019  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12714 cd/sqm

TEST NUMBER: P1287830

CATALOG NUMBER: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 32.6   | 10.3      |
| 10°-20°   | 76.4   | 24.1      |
| 20°-30°   | 84.2   | 26.6      |
| 30°-40°   | 63.1   | 19.9      |
| 40°-50°   | 32.7   | 10.3      |
| 50°-60°   | 13.5   | 4.3       |
| 60°-70°   | 8.4    | 2.6       |
| 70°-80°   | 4.7    | 1.5       |
| 80°-90°   | 1.4    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 193.2  | 61.0      |
| 0°-40°    | 256.3  | 80.9      |
| 0°-60°    | 302.5  | 95.5      |
| 0°-90°    | 316.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 316.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 365 |      |
| 5°  | 353 | 33   |
| 15° | 274 | 76   |
| 25° | 184 | 84   |
| 35° | 100 | 63   |
| 45° | 41  | 33   |
| 55° | 14  | 14   |
| 65° | 8   | 8    |
| 75° | 4   | 5    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1287830

CATALOG NUMBER: P3A05R15W2N902750DE010 E3DLD1WMH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 364.6 |
| 1°    | 365.0 |
| 2°    | 363.8 |
| 3°    | 361.4 |
| 4°    | 357.8 |
| 5°    | 353.4 |
| 6°    | 347.8 |
| 7°    | 341.8 |
| 8°    | 334.5 |
| 9°    | 326.9 |
| 10°   | 319.3 |
| 12.5° | 297.2 |
| 15°   | 274.3 |
| 17.5° | 251.4 |
| 20°   | 228.9 |
| 22.5° | 206.0 |
| 25°   | 184.3 |
| 27.5° | 162.6 |
| 30°   | 141.0 |
| 32.5° | 119.7 |
| 35°   | 100.0 |
| 37.5° | 83.1  |
| 40°   | 67.9  |
| 42.5° | 53.8  |
| 45°   | 41.0  |
| 47.5° | 30.9  |
| 50°   | 23.3  |
| 52.5° | 17.3  |
| 55°   | 14.1  |
| 57.5° | 12.4  |
| 60°   | 10.8  |
| 62.5° | 9.6   |
| 65°   | 8.4   |
| 67.5° | 7.2   |
| 70°   | 6.4   |
| 72.5° | 5.2   |
| 75°   | 4.4   |
| 77.5° | 3.6   |
| 80°   | 2.8   |
| 82.5° | 2.0   |
| 85°   | 1.2   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)