

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288089

Luminaire Tested: P3A05R20W2N902750DE010 E3CD1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R20W2N902750DE010 E3CD1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 453.1 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288089

CATALOG NUMBER: P3A05R20W2N902750DE010 E3CD1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1288089

CATALOG NUMBER: P3A05R20W2N902750DE010 E3CD1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101	100	99	98
2	112	109	106	104	110	108	105	103	104	103	101		102	100	99		99	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	94		97	95	93		96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		92	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703562
5°	610674
10°	377325
15°	131056
20°	40253
25°	14227
30°	5267
35°	2115
40°	1116
45°	434
50°	239
55°	268
60°	307
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 434 cd/sqm

TEST NUMBER: P1288089

CATALOG NUMBER: P3A05R20W2N902750DE010 E3CD1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.2	50.8
10°-20°	182.7	40.3
20°-30°	31.6	7.0
30°-40°	5.8	1.3
40°-50°	1.3	0.3
50°-60°	0.6	0.1
60°-70°	0.4	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.6	98.1
0°-40°	450.3	99.4
0°-60°	452.2	99.8
0°-90°	453.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	453.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3208	
5°	2774	230
15°	577	183
25°	59	32
35°	8	6
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288089

CATALOG NUMBER: P3A05R20W2N902750DE010 E3CD1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3208.5
1°	3193.1
2°	3132.1
3°	3034.2
4°	2919.5
5°	2774.3
6°	2607.9
7°	2414.3
8°	2193.7
9°	1946.0
10°	1694.6
12.5°	1068.9
15°	577.3
17.5°	308.4
20°	172.5
22.5°	98.6
25°	58.8
27.5°	35.9
30°	20.8
32.5°	12.2
35°	7.9
37.5°	5.4
40°	3.9
42.5°	2.5
45°	1.4
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)