

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292449

Luminaire Tested: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 183.0 lumens  
Efficiency: N/A  
Efficacy: 20.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292449  
CATALOG NUMBER: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292449

CATALOG NUMBER: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	66442
5°	63746
10°	55844
15°	44881
20°	34490
25°	26082
30°	18864
35°	12528
40°	7586
45°	4435
50°	2831
55°	2294
60°	2017
65°	1764
70°	1475
75°	1440
80°	1137
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4435 cd/sqm



TEST NUMBER: P1292449

CATALOG NUMBER: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.4	14.4
10°-20°	54.7	29.9
20°-30°	49.4	27.0
30°-40°	29.7	16.2
40°-50°	11.8	6.4
50°-60°	5.4	3.0
60°-70°	3.3	1.8
70°-80°	1.8	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	130.5	71.3
0°-40°	160.2	87.5
0°-60°	177.4	96.9
0°-90°	183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	183.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	303	
5°	290	26
15°	198	55
25°	108	49
35°	47	30
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1292449

CATALOG NUMBER: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	303.0
1°	303.0
2°	301.6
3°	298.4
4°	294.4
5°	289.6
6°	283.3
7°	276.2
8°	267.9
9°	259.6
10°	250.8
11°	240.5
12°	230.0
13°	219.4
14°	208.8
15°	197.7
17.5°	171.5
20°	147.8
22.5°	126.4
25°	107.8
27.5°	90.4
30°	74.5
32.5°	59.9
35°	46.8
37.5°	35.7
40°	26.5
42.5°	19.4
45°	14.3
47.5°	10.8
50°	8.3
52.5°	6.8
55°	6.0
57.5°	5.1
60°	4.6
62.5°	3.7
65°	3.4
67.5°	2.9
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.4
80°	0.9
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1292449  
CATALOG NUMBER: P3A09R25W2N902765DE010 E3DLP1GPH\_3000K

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

(END OF REPORT)