

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292488

Luminaire Tested: P3A09R25W2N902765DE010 E3PH1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R25W2N902765DE010 E3PH1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 625.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292488

CATALOG NUMBER: P3A09R25W2N902765DE010 E3PH1MW_5000K

Luminous Intensity Polar Plot



CATALOG NUMBER: P3A09R25W2N902765DE010 E3PH1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	98		
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	96		
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94		
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92		
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	90		
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	89		
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	87		
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	85		
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	84		
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	83		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	955910
5°	816419
10°	514709
15°	239547
20°	49331
25°	10065
30°	2152
35°	455
40°	229
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Luminance: 0 cd/sqm

TEST NUMBER: P1292488

CATALOG NUMBER: P3A09R25W2N902765DE010 E3PH1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.1	49.5
10°-20°	287.1	45.9
20°-30°	27.2	4.3
30°-40°	1.6	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.3	99.7
0°-40°	624.9	100.0
0°-60°	625.0	100.0
0°-90°	625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	625.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4359	
5°	3709	309
15°	1055	287
25°	42	27
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1292488

CATALOG NUMBER: P3A09R25W2N902765DE010 E3PH1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4359.3
2.5°	4197.1
5°	3709.0
7.5°	3049.4
10°	2311.6
12.5°	1669.9
15°	1055.2
17.5°	510.2
20°	211.4
22.5°	84.0
25°	41.6
27.5°	19.5
30°	8.5
32.5°	3.4
35°	1.7
37.5°	0.8
40°	0.8
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)