

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288498

Luminaire Tested: P3A05R25W2N902750DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288498
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R25W2N902750DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 257.0 lumens
Efficiency: N/A
Efficacy: 43.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288498
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1288498
 CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20							20
RC	80					70						30							10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50
RCR																			
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102
1	113	110	108	105		111	108	106	104		104	102	101		100	99	98		97
2	107	102	98	95		105	101	97	94		97	94	92		94	92	90		92
3	102	95	90	86		100	94	89	86		91	87	84		89	86	83		87
4	97	89	84	79		95	88	83	79		86	81	78		84	80	77		82
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70
8	80	70	65	60		79	70	64	60		69	64	60		68	63	60		67
9	76	67	61	57		75	66	61	57		65	60	57		65	60	57		64
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93304
5°	89522
10°	78422
15°	63042
20°	48421
25°	36655
30°	26485
35°	17587
40°	10677
45°	6202
50°	3957
55°	3211
60°	2807
65°	2491
70°	2052
75°	2033
80°	1515
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6202 cd/sqm



TEST NUMBER: P1288498

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.0	14.4
10°-20°	76.8	29.9
20°-30°	69.4	27.0
30°-40°	41.7	16.2
40°-50°	16.5	6.4
50°-60°	7.6	3.0
60°-70°	4.6	1.8
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.2	71.3
0°-40°	225.0	87.5
0°-60°	249.1	97.0
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	426	
5°	407	37
15°	278	77
25°	152	69
35°	66	42
45°	20	17
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1288498
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1WMH_4000K


CANDELA DISTRIBUTION (FULL):

0°	
0°	425.5
1°	425.5
2°	423.5
3°	419.1
4°	413.5
5°	406.7
6°	397.9
7°	387.8
8°	376.2
9°	364.6
10°	352.2
11°	337.8
12°	322.9
13°	308.1
14°	293.3
15°	277.7
17.5°	240.8
20°	207.5
22.5°	177.5
25°	151.5
27.5°	127.0
30°	104.6
32.5°	84.1
35°	65.7
37.5°	50.1
40°	37.3
42.5°	27.2
45°	20.0
47.5°	15.2
50°	11.6
52.5°	9.6
55°	8.4
57.5°	7.2
60°	6.4
62.5°	5.2
65°	4.8
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1288498
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)