

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288579

Luminaire Tested: P3A05R25W2N902765DE010 E3D1WMH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R25W2N902765DE010 E3D1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 540.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288579

CATALOG NUMBER: P3A05R25W2N902765DE010 E3D1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288579

CATALOG NUMBER: P3A05R25W2N902765DE010 E3D1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	97	97	97	94	94	94	92	92	92
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	96	94	94	94	92	92	92	90	90	90
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	93	92	92	92	90	90	90	88	88	88
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	91	94	92	90	89	89	87	87	87	85	85	85
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	93	91	89	89	88	86	86	85	85	85	83	83	83	81	81
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	88	86	86	85	85	85	83	83	83	81	81	81
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	86	85	85	85	83	83	83	81	81	81	79	79
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	84	83	83	83	81	81	81	79	79	79	77	77
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	82	81	81	81	79	79	79	77	77	77	75	75
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	80	79	79	79	77	77	77	75	75	75	73	73
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	78	77	77	77	75	75	75	73	73	73	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	591400
5°	547852
10°	423884
15°	202453
20°	66739
25°	28139
30°	10913
35°	4711
40°	1574
45°	713
50°	273
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1288579

CATALOG NUMBER: P3A05R25W2N902765DE010 E3D1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.8	40.5
10°-20°	248.8	46.1
20°-30°	57.8	10.7
30°-40°	12.1	2.2
40°-50°	2.0	0.4
50°-60°	0.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.4	97.3
0°-40°	537.6	99.5
0°-60°	539.8	100.0
0°-90°	540.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2697	
5°	2489	219
15°	892	249
25°	116	58
35°	18	12
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288579

CATALOG NUMBER: P3A05R25W2N902765DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2697.0
1°	2691.5
2°	2663.5
3°	2624.2
4°	2564.1
5°	2488.9
6°	2392.4
7°	2291.3
8°	2178.0
9°	2050.1
10°	1903.7
11°	1733.9
12°	1539.1
13°	1325.7
14°	1102.5
15°	891.8
16°	705.4
17°	549.6
18°	432.3
19°	345.8
20°	286.0
21°	239.1
22°	200.7
23°	167.6
24°	140.2
25°	116.3
27.5°	68.9
30°	43.1
32.5°	27.6
35°	17.6
37.5°	10.6
40°	5.5
42.5°	3.5
45°	2.3
47.5°	1.4
50°	0.8
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0



TEST NUMBER: P1288579

CATALOG NUMBER: P3A05R25W2N902765DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)