

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288765

Luminaire Tested: P3A05R30W2N902750DE010 E3DL1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R30W2N902750DE010 E3DL1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 208.1 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288765

CATALOG NUMBER: P3A05R30W2N902750DE010 E3DL1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288765

CATALOG NUMBER: P3A05R30W2N902750DE010 E3DL1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	95	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	86	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		78
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121372
5°	115518
10°	97170
15°	70080
20°	43474
25°	24727
30°	13724
35°	7469
40°	3950
45°	2140
50°	1126
55°	765
60°	702
65°	726
70°	641
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2140 cd/sqm

TEST NUMBER: P1288765

CATALOG NUMBER: P3A05R30W2N902750DE010 E3DL1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	22.7
10°-20°	84.0	40.4
20°-30°	48.6	23.3
30°-40°	18.4	8.9
40°-50°	5.7	2.7
50°-60°	1.9	0.9
60°-70°	1.3	0.6
70°-80°	0.7	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	179.8	86.4
0°-40°	198.3	95.3
0°-60°	205.8	98.9
0°-90°	208.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	208.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	525	47
15°	309	84
25°	102	49
35°	28	18
45°	7	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1288765

CATALOG NUMBER: P3A05R30W2N902750DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	553.5
1°	553.1
2°	549.8
3°	543.5
4°	535.6
5°	524.8
6°	511.1
7°	495.7
8°	478.6
9°	458.2
10°	436.4
11°	412.8
12°	387.9
13°	361.7
14°	335.2
15°	308.7
17.5°	243.5
20°	186.3
22.5°	138.1
25°	102.2
27.5°	74.3
30°	54.2
32.5°	39.1
35°	27.9
37.5°	19.5
40°	13.8
42.5°	9.6
45°	6.9
47.5°	4.7
50°	3.3
52.5°	2.4
55°	2.0
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.8
75°	0.6
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0



TEST NUMBER: P1288765

CATALOG NUMBER: P3A05R30W2N902750DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)