

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293107

Luminaire Tested: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1293107  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 476.0 lumens  
Efficiency: N/A  
Efficacy: 52.9 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293107

CATALOG NUMBER: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1293107

CATALOG NUMBER: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 94  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 75  | 72  | 78  | 74  | 71  | 69  |    |    |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  | 70  | 65  | 61  | 68  | 64  | 61  | 59  |    |    |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 56  | 55  |    |    |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 52  | 51  |    |    |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 48  |    |    |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 45  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 108741 |
| 5°  | 106427 |
| 10° | 99664  |
| 15° | 89467  |
| 20° | 77823  |
| 25° | 66318  |
| 30° | 55553  |
| 35° | 44250  |
| 40° | 32003  |
| 45° | 20250  |
| 50° | 11053  |
| 55° | 7646   |
| 60° | 7236   |
| 65° | 6693   |
| 70° | 6411   |
| 75° | 5507   |
| 80° | 5177   |
| 85° | 4529   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 20250 cd/sqm

TEST NUMBER: P1293107

CATALOG NUMBER: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.0   | 9.5       |
| 10°-20°   | 109.7  | 23.0      |
| 20°-30°   | 125.7  | 26.4      |
| 30°-40°   | 102.6  | 21.5      |
| 40°-50°   | 51.7   | 10.9      |
| 50°-60°   | 19.2   | 4.0       |
| 60°-70°   | 12.9   | 2.7       |
| 70°-80°   | 7.1    | 1.5       |
| 80°-90°   | 2.2    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 280.3  | 58.9      |
| 0°-40°    | 382.9  | 80.4      |
| 0°-60°    | 453.8  | 95.3      |
| 0°-90°    | 476.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 476.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 496 |      |
| 5°  | 484 | 45   |
| 15° | 394 | 110  |
| 25° | 274 | 126  |
| 35° | 165 | 103  |
| 45° | 65  | 52   |
| 55° | 20  | 19   |
| 65° | 13  | 13   |
| 75° | 6   | 7    |
| 85° | 2   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1293107

CATALOG NUMBER: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 495.9 |
| 1°    | 495.3 |
| 2°    | 494.1 |
| 3°    | 491.7 |
| 4°    | 488.2 |
| 5°    | 483.5 |
| 6°    | 477.6 |
| 7°    | 471.7 |
| 8°    | 464.1 |
| 9°    | 456.5 |
| 10°   | 447.6 |
| 11°   | 438.2 |
| 12°   | 428.2 |
| 13°   | 417.0 |
| 14°   | 405.3 |
| 15°   | 394.1 |
| 17.5° | 364.1 |
| 20°   | 333.5 |
| 22.5° | 302.3 |
| 25°   | 274.1 |
| 27.5° | 246.5 |
| 30°   | 219.4 |
| 32.5° | 192.3 |
| 35°   | 165.3 |
| 37.5° | 138.2 |
| 40°   | 111.8 |
| 42.5° | 87.1  |
| 45°   | 65.3  |
| 47.5° | 47.1  |
| 50°   | 32.4  |
| 52.5° | 23.5  |
| 55°   | 20.0  |
| 57.5° | 18.2  |
| 60°   | 16.5  |
| 62.5° | 14.7  |
| 65°   | 12.9  |
| 67.5° | 11.2  |
| 70°   | 10.0  |
| 72.5° | 8.2   |
| 75°   | 6.5   |
| 77.5° | 5.3   |
| 80°   | 4.1   |
| 82.5° | 2.9   |
| 85°   | 1.8   |
| 87.5° | 1.2   |



TEST NUMBER: P1293107

CATALOG NUMBER: P3A09R35W2N902765DE010 E3DLD1WMH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)