

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288862

Luminaire Tested: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1288862  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 201.0 lumens  
Efficiency: N/A  
Efficacy: 34.1 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288862

CATALOG NUMBER: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1288862

CATALOG NUMBER: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  |  | 98  | 96  | 94  |  | 95  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  |  | 91  | 88  | 85  |  | 88  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  |  | 79  | 74  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 67  | 62  | 82  | 72  | 66  | 62  | 71  | 65  | 61  |  | 69  | 64  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 57  | 67  | 61  | 57  |  | 66  | 60  | 57  |  | 64  |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 54  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 52  | 48  | 67  | 58  | 52  | 48  | 57  | 51  | 48  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 65258 |
| 5°  | 61545 |
| 10° | 52593 |
| 15° | 42157 |
| 20° | 32856 |
| 25° | 24703 |
| 30° | 18028 |
| 35° | 12715 |
| 40° | 8702  |
| 45° | 6233  |
| 50° | 5117  |
| 55° | 4932  |
| 60° | 4956  |
| 65° | 5085  |
| 70° | 5321  |
| 75° | 5676  |
| 80° | 5809  |
| 85° | 6542  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 6888 cd/sqm

TEST NUMBER: P1288862

CATALOG NUMBER: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 25.3   | 12.6      |
| 10°-20°   | 51.6   | 25.7      |
| 20°-30°   | 47.0   | 23.4      |
| 30°-40°   | 29.9   | 14.9      |
| 40°-50°   | 16.0   | 8.0       |
| 50°-60°   | 11.7   | 5.8       |
| 60°-70°   | 9.8    | 4.9       |
| 70°-80°   | 6.9    | 3.4       |
| 80°-90°   | 2.7    | 1.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 123.9  | 61.6      |
| 0°-40°    | 153.8  | 76.5      |
| 0°-60°    | 181.6  | 90.3      |
| 0°-90°    | 201.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 201.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 298 |      |
| 5°  | 280 | 25   |
| 15° | 186 | 52   |
| 25° | 102 | 47   |
| 35° | 48  | 30   |
| 45° | 20  | 16   |
| 55° | 13  | 12   |
| 65° | 10  | 10   |
| 75° | 7   | 7    |
| 85° | 3   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1288862

CATALOG NUMBER: P3A05R30W2N902750DE010 E3PHLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 297.6 |
| 2.5°  | 293.0 |
| 5°    | 279.6 |
| 7.5°  | 260.0 |
| 10°   | 236.2 |
| 12.5° | 211.0 |
| 15°   | 185.7 |
| 17.5° | 162.5 |
| 20°   | 140.8 |
| 22.5° | 120.7 |
| 25°   | 102.1 |
| 27.5° | 85.6  |
| 30°   | 71.2  |
| 32.5° | 57.8  |
| 35°   | 47.5  |
| 37.5° | 37.7  |
| 40°   | 30.4  |
| 42.5° | 24.2  |
| 45°   | 20.1  |
| 47.5° | 16.5  |
| 50°   | 15.0  |
| 52.5° | 13.9  |
| 55°   | 12.9  |
| 57.5° | 12.4  |
| 60°   | 11.3  |
| 62.5° | 10.8  |
| 65°   | 9.8   |
| 67.5° | 9.3   |
| 70°   | 8.3   |
| 72.5° | 7.2   |
| 75°   | 6.7   |
| 77.5° | 5.7   |
| 80°   | 4.6   |
| 82.5° | 4.1   |
| 85°   | 2.6   |
| 87.5° | 1.0   |
| 90°   | 0.0   |

(END OF REPORT)