

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289119

Luminaire Tested: P3A05R35W2N902750DE010 E3DL1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R35W2N902750DE010 E3DL1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 377.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289119
CATALOG NUMBER: P3A05R35W2N902750DE010 E3DL1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1289119

CATALOG NUMBER: P3A05R35W2N902750DE010 E3DL1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	190138
5°	182742
10°	159227
15°	121953
20°	81580
25°	49358
30°	28333
35°	15847
40°	8416
45°	4342
50°	2081
55°	1644
60°	1579
65°	1297
70°	1410
75°	1186
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4342 cd/sqm



TEST NUMBER: P1289119

CATALOG NUMBER: P3A05R35W2N902750DE010 E3DL1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	20.0
10°-20°	146.4	38.8
20°-30°	95.8	25.4
30°-40°	38.9	10.3
40°-50°	11.7	3.1
50°-60°	4.0	1.1
60°-70°	2.7	0.7
70°-80°	1.6	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	317.7	84.3
0°-40°	356.6	94.6
0°-60°	372.2	98.7
0°-90°	377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	377.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	867	
5°	830	76
15°	537	146
25°	204	96
35°	59	39
45°	14	12
55°	4	4
65°	2	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P1289119

CATALOG NUMBER: P3A05R35W2N902750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	867.1
1°	865.7
2°	861.7
3°	853.9
4°	844.5
5°	830.2
6°	812.3
7°	792.2
8°	769.6
9°	743.8
10°	715.1
11°	683.2
12°	649.8
13°	612.5
14°	577.0
15°	537.2
17.5°	440.7
20°	349.6
22.5°	269.0
25°	204.0
27.5°	152.1
30°	111.9
32.5°	82.1
35°	59.2
37.5°	42.0
40°	29.4
42.5°	20.4
45°	14.0
47.5°	9.3
50°	6.1
52.5°	4.7
55°	4.3
57.5°	3.9
60°	3.6
62.5°	3.2
65°	2.5
67.5°	2.2
70°	2.2
72.5°	1.8
75°	1.4
77.5°	1.1
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4



TEST NUMBER: P1289119
CATALOG NUMBER: P3A05R35W2N902750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)