

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293745

Luminaire Tested: P3A09R45W2N902765DE010 E3DLP1WH\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1293745  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R45W2N902765DE010 E3DLP1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 652.0 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293745

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLP1WH\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1293745

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLP1WH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |     |     |     | 0   |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 93  | 91  | 90  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 86  | 84  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  |
| 6   | 90  | 82  | 77  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 64  | 72  | 68  | 64  | 71  | 67  | 64  | 70  | 67  | 64  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 61  | 58  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 244849 |
| 5°  | 239115 |
| 10° | 219813 |
| 15° | 186244 |
| 20° | 144493 |
| 25° | 101014 |
| 30° | 63630  |
| 35° | 37450  |
| 40° | 21211  |
| 45° | 10296  |
| 50° | 3582   |
| 55° | 2906   |
| 60° | 2807   |
| 65° | 2698   |
| 70° | 2629   |
| 75° | 2457   |
| 80° | 2147   |
| 85° | 1510   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 10296 cd/sqm

TEST NUMBER: P1293745

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLP1WH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 100.6  | 15.4      |
| 10°-20°   | 225.3  | 34.6      |
| 20°-30°   | 191.3  | 29.3      |
| 30°-40°   | 91.3   | 14.0      |
| 40°-50°   | 27.5   | 4.2       |
| 50°-60°   | 7.0    | 1.1       |
| 60°-70°   | 5.2    | 0.8       |
| 70°-80°   | 3.1    | 0.5       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 517.2  | 79.3      |
| 0°-40°    | 608.4  | 93.3      |
| 0°-60°    | 642.9  | 98.6      |
| 0°-90°    | 652.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 652.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1117 |      |
| 5°  | 1086 | 101  |
| 15° | 820  | 225  |
| 25° | 418  | 191  |
| 35° | 140  | 91   |
| 45° | 33   | 27   |
| 55° | 8    | 7    |
| 65° | 5    | 5    |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1293745

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLP1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1116.6 |
| 2.5°  | 1109.6 |
| 5°    | 1086.3 |
| 7.5°  | 1046.0 |
| 10°   | 987.2  |
| 12.5° | 909.0  |
| 15°   | 820.4  |
| 17.5° | 721.9  |
| 20°   | 619.2  |
| 22.5° | 514.9  |
| 25°   | 417.5  |
| 27.5° | 328.9  |
| 30°   | 251.3  |
| 32.5° | 188.9  |
| 35°   | 139.9  |
| 37.5° | 103.2  |
| 40°   | 74.1   |
| 42.5° | 51.3   |
| 45°   | 33.2   |
| 47.5° | 18.7   |
| 50°   | 10.5   |
| 52.5° | 8.2    |
| 55°   | 7.6    |
| 57.5° | 7.0    |
| 60°   | 6.4    |
| 62.5° | 5.8    |
| 65°   | 5.2    |
| 67.5° | 4.7    |
| 70°   | 4.1    |
| 72.5° | 3.5    |
| 75°   | 2.9    |
| 77.5° | 2.3    |
| 80°   | 1.7    |
| 82.5° | 1.2    |
| 85°   | 0.6    |
| 87.5° | 0.6    |
| 90°   | 0.0    |

(END OF REPORT)