

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289278

Luminaire Tested: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R35W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289278
CATALOG NUMBER: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1289278

CATALOG NUMBER: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35874
5°	35109
10°	32865
15°	29512
20°	25669
25°	21872
30°	18332
35°	14589
40°	10563
45°	6667
50°	3650
55°	2523
60°	2368
65°	2231
70°	2116
75°	1779
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6667 cd/sqm



TEST NUMBER: P1289278

CATALOG NUMBER: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.8	9.5
10°-20°	36.2	23.0
20°-30°	41.5	26.4
30°-40°	33.8	21.5
40°-50°	17.1	10.9
50°-60°	6.3	4.0
60°-70°	4.3	2.7
70°-80°	2.3	1.5
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	92.5	58.9
0°-40°	126.3	80.4
0°-60°	149.7	95.3
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	164	
5°	160	15
15°	130	36
25°	90	41
35°	54	34
45°	22	17
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1289278
CATALOG NUMBER: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	163.6
1°	163.4
2°	163.0
3°	162.2
4°	161.0
5°	159.5
6°	157.5
7°	155.6
8°	153.1
9°	150.6
10°	147.6
11°	144.5
12°	141.2
13°	137.6
14°	133.7
15°	130.0
17.5°	120.1
20°	110.0
22.5°	99.7
25°	90.4
27.5°	81.3
30°	72.4
32.5°	63.4
35°	54.5
37.5°	45.6
40°	36.9
42.5°	28.7
45°	21.5
47.5°	15.5
50°	10.7
52.5°	7.8
55°	6.6
57.5°	6.0
60°	5.4
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.3
72.5°	2.7
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.4



TEST NUMBER: P1289278
CATALOG NUMBER: P3A05R35W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)