

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293767

Luminaire Tested: P3A09R50W2N902750DE010 E3CB1MW\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1293767  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R50W2N902750DE010 E3CB1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,  
E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 798.0 lumens  
Efficiency: N/A  
Efficacy: 88.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293767

CATALOG NUMBER: P3A09R50W2N902750DE010 E3CB1MW\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1293767

CATALOG NUMBER: P3A09R50W2N902750DE010 E3CB1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 101 | 99  | 98  | 97  | 96  | 96  | 96  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 93  | 91  | 91  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 86  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 92  | 88  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 87  | 84  | 82  | 82  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 94  | 88  | 83  | 79  | 86  | 82  | 79  | 84  | 81  | 78  | 83  | 80  | 77  | 77  | 77  | 76  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 73  | 73  | 72  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 70  | 70  | 69  |
| 8   | 85  | 76  | 71  | 67  | 83  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 66  | 66  | 66  | 65  |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 67  | 64  | 71  | 67  | 64  | 71  | 66  | 63  | 70  | 66  | 63  | 63  | 63  | 62  |
| 10  | 78  | 69  | 64  | 61  | 77  | 69  | 64  | 61  | 68  | 64  | 61  | 68  | 63  | 61  | 67  | 63  | 60  | 60  | 60  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 277916 |
| 5°  | 272947 |
| 10° | 262075 |
| 15° | 240319 |
| 20° | 211908 |
| 25° | 162421 |
| 30° | 88317  |
| 35° | 28429  |
| 40° | 6670   |
| 45° | 899    |
| 50° | 785    |
| 55° | 879    |
| 60° | 746    |
| 65° | 882    |
| 70° | 769    |
| 75° | 1017   |
| 80° | 758    |
| 85° | 1510   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 85°  
Luminance: 1510 cd/sqm

TEST NUMBER: P1293767

CATALOG NUMBER: P3A09R50W2N902750DE010 E3CB1MW\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 116.4  | 14.6      |
| 10°-20°   | 294.3  | 36.9      |
| 20°-30°   | 294.7  | 36.9      |
| 30°-40°   | 82.9   | 10.4      |
| 40°-50°   | 5.0    | 0.6       |
| 50°-60°   | 1.9    | 0.2       |
| 60°-70°   | 1.5    | 0.2       |
| 70°-80°   | 1.0    | 0.1       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 705.3  | 88.4      |
| 0°-40°    | 788.2  | 98.8      |
| 0°-60°    | 795.0  | 99.6      |
| 0°-90°    | 798.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 798.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1267 |      |
| 5°  | 1240 | 116  |
| 15° | 1059 | 294  |
| 25° | 671  | 295  |
| 35° | 106  | 83   |
| 45° | 3    | 5    |
| 55° | 2    | 2    |
| 65° | 2    | 1    |
| 75° | 1    | 1    |
| 85° | 1    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1293767

CATALOG NUMBER: P3A09R50W2N902750DE010 E3CB1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1267.4 |
| 2.5°  | 1261.0 |
| 5°    | 1240.0 |
| 7.5°  | 1211.4 |
| 10°   | 1177.0 |
| 12.5° | 1125.1 |
| 15°   | 1058.6 |
| 17.5° | 982.2  |
| 20°   | 908.1  |
| 22.5° | 816.0  |
| 25°   | 671.3  |
| 27.5° | 499.8  |
| 30°   | 348.8  |
| 32.5° | 210.6  |
| 35°   | 106.2  |
| 37.5° | 50.2   |
| 40°   | 23.3   |
| 42.5° | 8.7    |
| 45°   | 2.9    |
| 47.5° | 2.3    |
| 50°   | 2.3    |
| 52.5° | 2.3    |
| 55°   | 2.3    |
| 57.5° | 1.7    |
| 60°   | 1.7    |
| 62.5° | 1.7    |
| 65°   | 1.7    |
| 67.5° | 1.2    |
| 70°   | 1.2    |
| 72.5° | 1.2    |
| 75°   | 1.2    |
| 77.5° | 0.6    |
| 80°   | 0.6    |
| 82.5° | 0.6    |
| 85°   | 0.6    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)