

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293965

Luminaire Tested: P3A09R50W2N902765DE010 E3D1WMH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R50W2N902765DE010 E3D1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 817.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293965

CATALOG NUMBER: P3A09R50W2N902765DE010 E3D1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293965

CATALOG NUMBER: P3A09R50W2N902765DE010 E3D1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80		
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68		
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285503
5°	277899
10°	265192
15°	240092
20°	207708
25°	170381
30°	97863
35°	30410
40°	8158
45°	2853
50°	682
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2853 cd/sqm

TEST NUMBER: P1293965

CATALOG NUMBER: P3A09R50W2N902765DE010 E3D1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	14.5
10°-20°	293.0	35.9
20°-30°	308.0	37.7
30°-40°	88.1	10.8
40°-50°	8.6	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.3	88.0
0°-40°	807.4	98.8
0°-60°	816.8	100.0
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1302	
5°	1262	118
15°	1058	293
25°	704	308
35°	114	88
45°	9	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1293965

CATALOG NUMBER: P3A09R50W2N902765DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1302.0
1°	1300.0
2°	1294.2
3°	1285.9
4°	1274.6
5°	1262.5
6°	1249.6
7°	1235.7
8°	1222.8
9°	1207.8
10°	1191.0
11°	1171.7
12°	1149.5
13°	1121.9
14°	1091.9
15°	1057.6
16°	1021.3
17°	986.1
18°	950.1
19°	918.4
20°	890.1
21°	863.0
22°	832.2
23°	796.7
24°	755.2
25°	704.2
26°	648.9
27°	587.2
28°	525.8
29°	459.5
30°	386.5
31°	318.2
32°	255.4
32.5°	228.0
33°	200.3
34°	153.6
35°	113.6
36°	83.3
37°	62.0
37.5°	53.6
38°	46.4
39°	36.0
40°	28.5
42.5°	16.1
45°	9.2



TEST NUMBER: P1293965

CATALOG NUMBER: P3A09R50W2N902765DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.2
50°	2.0
52.5°	0.9
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)