

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293998

Luminaire Tested: P3A09R50W2N902765DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R50W2N902765DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 656.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293998

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1293998

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75	72	69	67
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68	64	61	60
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208865
5°	204644
10°	191691
15°	171601
20°	144399
25°	110208
30°	71631
35°	42456
40°	24532
45°	12311
50°	4571
55°	3555
60°	3333
65°	3009
70°	3013
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12311 cd/sqm

TEST NUMBER: P1293998

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.5	13.2
10°-20°	209.0	31.9
20°-30°	205.1	31.3
30°-40°	103.3	15.7
40°-50°	32.6	5.0
50°-60°	8.5	1.3
60°-70°	6.0	0.9
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.6	76.3
0°-40°	603.9	92.1
0°-60°	645.0	98.3
0°-90°	656.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	656.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	930	86
15°	756	209
25°	456	205
35°	159	103
45°	40	33
55°	9	8
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1293998

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	952.5
2.5°	946.6
5°	929.7
7.5°	899.4
10°	860.9
12.5°	811.3
15°	755.9
17.5°	691.8
20°	618.8
22.5°	540.1
25°	455.5
27.5°	365.7
30°	282.9
32.5°	212.9
35°	158.6
37.5°	117.2
40°	85.7
42.5°	60.7
45°	39.7
47.5°	22.7
50°	13.4
52.5°	9.9
55°	9.3
57.5°	8.2
60°	7.6
62.5°	7.0
65°	5.8
67.5°	5.2
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)