

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289487

Luminaire Tested: P3A05R40W2N902750DE010 E3DLP1H\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1289487  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRIS  
Catalog Number: P3A05R40W2N902750DE010 E3DLP1H\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 263.0 lumens  
Efficiency: N/A  
Efficacy: 44.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289487  
CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLP1H\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1289487  
 CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLP1H\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81901
5°	80233
10°	74704
15°	65108
20°	52481
25°	39341
30°	27650
35°	18123
40°	10963
45°	6543
50°	3923
55°	3135
60°	2807
65°	2439
70°	2308
75°	1779
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6543 cd/sqm



TEST NUMBER: P1289487

CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLP1H\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.8	12.9
10°-20°	79.0	30.0
20°-30°	74.4	28.3
30°-40°	43.0	16.4
40°-50°	17.1	6.5
50°-60°	7.6	2.9
60°-70°	4.7	1.8
70°-80°	2.5	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	187.3	71.2
0°-40°	230.3	87.6
0°-60°	255.1	97.0
0°-90°	263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	263.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	374	
5°	364	34
15°	287	79
25°	163	74
35°	68	43
45°	21	17
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1289487  
CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLP1H\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	373.5
2.5°	371.3
5°	364.5
7.5°	352.0
10°	335.5
12.5°	313.3
15°	286.8
17.5°	257.1
20°	224.9
22.5°	192.6
25°	162.6
27.5°	134.6
30°	109.2
32.5°	87.0
35°	67.7
37.5°	51.2
40°	38.3
42.5°	28.6
45°	21.1
47.5°	15.4
50°	11.5
52.5°	9.3
55°	8.2
57.5°	7.5
60°	6.4
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.6
72.5°	2.9
75°	2.1
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)