

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289571

Luminaire Tested: P3A05R40W2N902765DE010 E3D1WH_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R40W2N902765DE010 E3D1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 559.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289571

CATALOG NUMBER: P3A05R40W2N902765DE010 E3D1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1289571

CATALOG NUMBER: P3A05R40W2N902765DE010 E3D1WH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	109		112	110	109	107		106	105	104		103	102	101		99	98	98
2	111	107	104	101		109	105	102	100		102	100	98		99	97	96		96	95	94
3	107	102	98	95		105	100	97	94		98	95	93		96	93	91		93	91	90
4	103	97	93	90		101	96	92	89		94	91	88		92	89	87		90	88	86
5	99	93	89	85		98	92	88	85		91	87	84		89	86	84		88	85	83
6	96	89	85	81		95	89	84	81		87	83	81		86	83	80		85	82	80
7	93	86	81	78		92	85	81	78		84	80	77		83	80	77		82	79	77
8	90	83	78	75		89	82	78	75		81	77	75		80	77	74		79	76	74
9	87	80	75	72		86	79	75	72		78	75	72		78	74	72		77	74	71
10	84	77	72	70		83	77	72	69		76	72	69		75	72	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284933
5°	282874
10°	275479
15°	246063
20°	163161
25°	61116
30°	16357
35°	6398
40°	2290
45°	1085
50°	341
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1085 cd/sqm

TEST NUMBER: P1289571

CATALOG NUMBER: P3A05R40W2N902765DE010 E3D1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	21.7
10°-20°	287.2	51.4
20°-30°	130.2	23.3
30°-40°	16.9	3.0
40°-50°	2.9	0.5
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.7	96.4
0°-40°	555.6	99.4
0°-60°	558.9	100.0
0°-90°	559.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	559.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1299	
5°	1285	121
15°	1084	287
25°	253	130
35°	24	17
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1289571

CATALOG NUMBER: P3A05R40W2N902765DE010 E3D1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.4
1°	1298.6
2°	1296.7
3°	1293.7
4°	1290.0
5°	1285.1
6°	1279.4
7°	1272.4
8°	1263.8
9°	1252.1
10°	1237.2
11°	1219.8
12°	1196.5
13°	1167.7
14°	1130.1
15°	1083.9
16°	1025.0
17°	957.9
18°	877.3
19°	792.2
20°	699.2
21°	606.3
22°	514.7
23°	423.5
24°	333.9
25°	252.6
26°	187.1
27°	137.0
28°	102.9
29°	80.0
30°	64.6
31°	53.4
32°	44.6
32.5°	40.7
33°	36.8
34°	29.9
35°	23.9
36°	18.8
37°	14.9
37.5°	13.3
38°	11.7
39°	9.8
40°	8.0
42.5°	5.3
45°	3.5



TEST NUMBER: P1289571

CATALOG NUMBER: P3A05R40W2N902765DE010 E3D1WH_6500K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.2
50°	1.0
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)