

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294130

Luminaire Tested: P3A09R55W2N902750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R55W2N902750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 282.0 lumens
Efficiency: N/A
Efficacy: 31.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294130

CATALOG NUMBER: P3A09R55W2N902750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1294130

CATALOG NUMBER: P3A09R55W2N902750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77428
5°	76645
10°	74013
15°	68423
20°	59038
25°	46624
30°	33068
35°	21335
40°	12824
45°	7226
50°	3889
55°	1376
60°	1228
65°	1193
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7226 cd/sqm

TEST NUMBER: P1294130

CATALOG NUMBER: P3A09R55W2N902750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.7	11.6
10°-20°	83.3	29.6
20°-30°	87.3	31.0
30°-40°	50.9	18.1
40°-50°	19.1	6.8
50°-60°	4.5	1.6
60°-70°	2.3	0.8
70°-80°	1.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.4	72.1
0°-40°	254.4	90.2
0°-60°	277.9	98.6
0°-90°	282.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	282.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	353	
5°	348	33
15°	301	83
25°	193	87
35°	80	51
45°	23	19
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1294130

CATALOG NUMBER: P3A09R55W2N902750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	353.1
2.5°	352.1
5°	348.2
7.5°	342.0
10°	332.4
12.5°	319.0
15°	301.4
17.5°	279.1
20°	253.0
22.5°	223.8
25°	192.7
27.5°	160.9
30°	130.6
32.5°	103.2
35°	79.7
37.5°	60.5
40°	44.8
42.5°	32.1
45°	23.3
47.5°	16.8
50°	11.4
52.5°	6.5
55°	3.6
57.5°	3.1
60°	2.8
62.5°	2.6
65°	2.3
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)