

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289924

Luminaire Tested: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 6500K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 346.1 lumens  
Efficiency: N/A  
Efficacy: 58.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289924

CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289924

CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 96  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 83  | 80  |  | 85  | 81  | 78  |  | 83  |
| 4   | 94  | 85  | 78  | 74  | 92  | 84  | 78  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 66  | 61  | 71  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 7   | 78  | 68  | 61  | 57  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 65  | 60  | 56  |  | 64  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  |
| 9   | 70  | 60  | 53  | 49  | 69  | 59  | 53  | 49  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 67  | 56  | 50  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 45  |  | 54  | 49  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 73349 |
| 5°  | 72067 |
| 10° | 68180 |
| 15° | 62180 |
| 20° | 55001 |
| 25° | 47761 |
| 30° | 40994 |
| 35° | 34158 |
| 40° | 25448 |
| 45° | 15568 |
| 50° | 7198  |
| 55° | 5658  |
| 60° | 5438  |
| 65° | 4981  |
| 70° | 4616  |
| 75° | 4406  |
| 80° | 4041  |
| 85° | 3019  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15568 cd/sqm

TEST NUMBER: P1289924

CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 30.6   | 8.8       |
| 10°-20°   | 76.3   | 22.0      |
| 20°-30°   | 90.6   | 26.2      |
| 30°-40°   | 78.7   | 22.8      |
| 40°-50°   | 39.5   | 11.4      |
| 50°-60°   | 13.7   | 4.0       |
| 60°-70°   | 9.6    | 2.8       |
| 70°-80°   | 5.4    | 1.6       |
| 80°-90°   | 1.6    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 197.5  | 57.1      |
| 0°-40°    | 276.2  | 79.8      |
| 0°-60°    | 329.4  | 95.2      |
| 0°-90°    | 346.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 346.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 334 |      |
| 5°  | 327 | 31   |
| 15° | 274 | 76   |
| 25° | 197 | 91   |
| 35° | 128 | 79   |
| 45° | 50  | 39   |
| 55° | 15  | 14   |
| 65° | 10  | 10   |
| 75° | 5   | 5    |
| 85° | 1   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1289924

CATALOG NUMBER: P3A05R45W2N902765DE010 E3DLD1WMH\_6500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 334.5 |
| 2.5°  | 333.0 |
| 5°    | 327.4 |
| 7.5°  | 318.6 |
| 10°   | 306.2 |
| 12.5° | 291.1 |
| 15°   | 273.9 |
| 17.5° | 254.8 |
| 20°   | 235.7 |
| 22.5° | 216.1 |
| 25°   | 197.4 |
| 27.5° | 179.4 |
| 30°   | 161.9 |
| 32.5° | 145.1 |
| 35°   | 127.6 |
| 37.5° | 108.9 |
| 40°   | 88.9  |
| 42.5° | 69.4  |
| 45°   | 50.2  |
| 47.5° | 33.1  |
| 50°   | 21.1  |
| 52.5° | 16.3  |
| 55°   | 14.8  |
| 57.5° | 13.6  |
| 60°   | 12.4  |
| 62.5° | 11.2  |
| 65°   | 9.6   |
| 67.5° | 8.4   |
| 70°   | 7.2   |
| 72.5° | 6.0   |
| 75°   | 5.2   |
| 77.5° | 4.0   |
| 80°   | 3.2   |
| 82.5° | 2.4   |
| 85°   | 1.2   |
| 87.5° | 0.8   |
| 90°   | 0.0   |

(END OF REPORT)