

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302974

Luminaire Tested: P3DUS05R509024DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS05R509024DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 641.0 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302974  
CATALOG NUMBER: P3DUS05R509024DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1302974  
 CATALOG NUMBER: P3DUS05R509024DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82	82	82	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	78	78	78	78
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74	74	74	74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70	70	70	70
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67	67	67	67
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	258422
5°	252234
10°	238294
15°	209422
20°	157537
25°	116474
30°	70669
35°	23370
40°	4122
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1302974  
 CATALOG NUMBER: P3DUS05R509024DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.0	16.7
10°-20°	250.9	39.1
20°-30°	215.1	33.6
30°-40°	66.4	10.4
40°-50°	1.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	573.0	89.4
0°-40°	639.4	99.7
0°-60°	641.0	100.0
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1178	
5°	1146	107
15°	922	251
25°	481	215
35°	87	66
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1302974  
CATALOG NUMBER: P3DUS05R509024DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1178.5
2.5°	1169.9
5°	1145.9
7.5°	1112.4
10°	1070.2
12.5°	1003.1
15°	922.5
17.5°	819.9
20°	675.1
22.5°	552.4
25°	481.4
27.5°	391.2
30°	279.1
32.5°	169.7
35°	87.3
37.5°	39.3
40°	14.4
42.5°	1.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)