

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302995

Luminaire Tested: P3DUS09R359024DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R359024DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 901.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302995

CATALOG NUMBER: P3DUS09R359024DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1302995

CATALOG NUMBER: P3DUS09R359024DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	90	94	92	89	92	90	89	88	87	86
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85	84	83
6	98	92	88	85	97	91	87	85	90	87	84	89	86	83	88	85	83	82	81	80
7	95	89	85	82	94	88	84	82	87	84	81	86	83	81	85	83	80	79	78	77
8	93	86	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77	76	75
9	90	83	79	77	89	83	79	76	82	79	76	82	78	76	81	78	76	75	74	73
10	88	81	77	74	87	81	77	74	80	76	74	79	76	74	79	76	74	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	660035
5°	640346
10°	570998
15°	403385
20°	194570
25°	63052
30°	17750
35°	7121
40°	2004
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1302995

CATALOG NUMBER: P3DUS09R359024DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.2	29.7
10°-20°	469.6	52.1
20°-30°	144.3	16.0
30°-40°	18.8	2.1
40°-50°	1.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.1	97.8
0°-40°	899.8	99.9
0°-60°	901.0	100.0
0°-90°	901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3010	
5°	2909	267
15°	1777	470
25°	261	144
35°	27	19
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1302995

CATALOG NUMBER: P3DUS09R359024DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3010.0
2.5°	2986.2
5°	2909.1
7.5°	2781.6
10°	2564.4
12.5°	2225.3
15°	1776.9
17.5°	1289.2
20°	833.8
22.5°	483.5
25°	260.6
27.5°	137.3
30°	70.1
32.5°	42.0
35°	26.6
37.5°	16.8
40°	7.0
42.5°	2.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)