

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303142

Luminaire Tested: P3DUS05R409027DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R409027DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 687.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303142

CATALOG NUMBER: P3DUS05R409027DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303142

CATALOG NUMBER: P3DUS05R409027DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	97	96	94
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	94	93	91
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	94	93	91
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	92	90	88
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	89	87	85
6	98	91	87	84	96	90	86	84	89	86	83	88	85	83	87	84	82	87	84	82
7	95	88	84	81	94	87	83	80	86	83	80	85	82	80	84	81	79	84	81	79
8	92	85	81	78	91	85	80	78	84	80	77	83	79	77	82	79	77	82	79	77
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	80	77	74
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	77	74	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	422378
5°	418423
10°	393424
15°	324156
20°	179519
25°	52068
30°	12837
35°	4631
40°	1174
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303142

CATALOG NUMBER: P3DUS05R409027DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.3	25.8
10°-20°	373.7	54.4
20°-30°	123.0	17.9
30°-40°	12.4	1.8
40°-50°	0.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	674.1	98.1
0°-40°	686.4	99.9
0°-60°	687.0	100.0
0°-90°	687.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1926	
5°	1901	177
15°	1428	374
25°	215	123
35°	17	12
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303142

CATALOG NUMBER: P3DUS05R409027DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1926.2
2.5°	1923.2
5°	1900.9
7.5°	1854.2
10°	1766.9
12.5°	1631.9
15°	1427.9
17.5°	1146.8
20°	769.3
22.5°	415.1
25°	215.2
27.5°	102.5
30°	50.7
32.5°	28.4
35°	17.3
37.5°	9.1
40°	4.1
42.5°	1.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)