

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290358

Luminaire Tested: P3A05R55W2N902750DE010 E3DL1WH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290358  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R55W2N902750DE010 E3DL1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 292.0 lumens  
Efficiency: N/A  
Efficacy: 49.5 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290358

CATALOG NUMBER: P3A05R55W2N902750DE010 E3DL1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1290358

CATALOG NUMBER: P3A05R55W2N902750DE010 E3DL1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 97  | 95  | 94  | 92  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 93  | 97  | 93  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  | 85  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 84  | 81  |  | 85  | 83  | 80  | 79  |
| 4   | 96  | 88  | 82  | 77  | 94  | 87  | 81  | 77  | 84  | 80  | 76  |  | 82  | 78  | 75  |  | 80  | 77  | 74  | 73  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 69  | 67  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 64  | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  |  | 69  | 64  | 60  |  | 68  | 63  | 60  | 59  |
| 8   | 78  | 68  | 62  | 57  | 76  | 67  | 61  | 57  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  | 60  | 56  | 55  |
| 9   | 74  | 64  | 58  | 54  | 73  | 63  | 58  | 54  | 62  | 57  | 53  |  | 62  | 57  | 53  |  | 61  | 56  | 53  | 52  |
| 10  | 70  | 60  | 55  | 51  | 69  | 60  | 54  | 50  | 59  | 54  | 50  |  | 58  | 54  | 50  |  | 58  | 53  | 50  | 49  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 79423 |
| 5°  | 77438 |
| 10° | 71987 |
| 15° | 64109 |
| 20° | 54488 |
| 25° | 43962 |
| 30° | 33524 |
| 35° | 23851 |
| 40° | 15744 |
| 45° | 9334  |
| 50° | 5458  |
| 55° | 3364  |
| 60° | 2982  |
| 65° | 2698  |
| 70° | 2308  |
| 75° | 2033  |
| 80° | 2020  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 9334 cd/sqm

TEST NUMBER: P1290358

CATALOG NUMBER: P3A05R55W2N902750DE010 E3DL1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 32.7   | 11.2      |
| 10°-20°   | 78.3   | 26.8      |
| 20°-30°   | 82.9   | 28.4      |
| 30°-40°   | 56.0   | 19.2      |
| 40°-50°   | 24.6   | 8.4       |
| 50°-60°   | 8.8    | 3.0       |
| 60°-70°   | 5.1    | 1.8       |
| 70°-80°   | 2.7    | 0.9       |
| 80°-90°   | 0.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 193.9  | 66.4      |
| 0°-40°    | 249.9  | 85.6      |
| 0°-60°    | 283.3  | 97.0      |
| 0°-90°    | 292.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 292.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 362 |      |
| 5°  | 352 | 33   |
| 15° | 282 | 78   |
| 25° | 182 | 83   |
| 35° | 89  | 56   |
| 45° | 30  | 25   |
| 55° | 9   | 9    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1290358

CATALOG NUMBER: P3A05R55W2N902750DE010 E3DL1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 362.2 |
| 2.5°  | 359.4 |
| 5°    | 351.8 |
| 7.5°  | 339.4 |
| 10°   | 323.3 |
| 12.5° | 304.1 |
| 15°   | 282.4 |
| 17.5° | 258.3 |
| 20°   | 233.5 |
| 22.5° | 207.4 |
| 25°   | 181.7 |
| 27.5° | 156.5 |
| 30°   | 132.4 |
| 32.5° | 109.5 |
| 35°   | 89.1  |
| 37.5° | 70.6  |
| 40°   | 55.0  |
| 42.5° | 41.3  |
| 45°   | 30.1  |
| 47.5° | 22.1  |
| 50°   | 16.0  |
| 52.5° | 11.2  |
| 55°   | 8.8   |
| 57.5° | 8.0   |
| 60°   | 6.8   |
| 62.5° | 6.0   |
| 65°   | 5.2   |
| 67.5° | 4.4   |
| 70°   | 3.6   |
| 72.5° | 3.2   |
| 75°   | 2.4   |
| 77.5° | 2.0   |
| 80°   | 1.6   |
| 82.5° | 1.2   |
| 85°   | 0.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)