

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290410

Luminaire Tested: P3A05R55W2N902750DE010 E3DLP1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R55W2N902750DE010 E3DLP1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 261.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290410
CATALOG NUMBER: P3A05R55W2N902750DE010 E3DLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290410
 CATALOG NUMBER: P3A05R55W2N902750DE010 E3DLP1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55			55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52			52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71003
5°	69227
10°	64350
15°	57299
20°	48701
25°	39293
30°	29954
35°	21308
40°	14055
45°	8342
50°	4878
55°	3020
60°	2675
65°	2439
70°	2052
75°	1864
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8342 cd/sqm



TEST NUMBER: P1290410

CATALOG NUMBER: P3A05R55W2N902750DE010 E3DLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	11.2
10°-20°	70.0	26.8
20°-30°	74.1	28.4
30°-40°	50.1	19.2
40°-50°	21.9	8.4
50°-60°	7.9	3.0
60°-70°	4.6	1.8
70°-80°	2.4	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	66.4
0°-40°	223.4	85.6
0°-60°	253.2	97.0
0°-90°	261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	324	
5°	314	29
15°	252	70
25°	162	74
35°	80	50
45°	27	22
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1290410
CATALOG NUMBER: P3A05R55W2N902750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	323.8
2.5°	321.3
5°	314.5
7.5°	303.3
10°	289.0
12.5°	271.8
15°	252.4
17.5°	230.9
20°	208.7
22.5°	185.4
25°	162.4
27.5°	139.8
30°	118.3
32.5°	97.9
35°	79.6
37.5°	63.1
40°	49.1
42.5°	36.9
45°	26.9
47.5°	19.7
50°	14.3
52.5°	10.0
55°	7.9
57.5°	7.2
60°	6.1
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.2
72.5°	2.9
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)