

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303570

Luminaire Tested: P3DUS17R359035DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R359035DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1849.0 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303570

CATALOG NUMBER: P3DUS17R359035DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1303570

CATALOG NUMBER: P3DUS17R359035DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	105	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	99	97	106	102	98	96	99	97	94		97	95	93		95
4	104	99	95	92	103	98	94	92	96	93	90		94	92	89		92
5	101	95	91	88	100	94	91	88	93	90	87		91	89	86		90
6	98	92	88	85	97	91	87	85	90	87	84		89	86	83		88
7	95	89	85	82	94	88	84	82	87	84	81		86	83	81		85
8	93	86	82	79	92	86	82	79	85	81	79		84	81	78		83
9	90	83	79	77	89	83	79	76	82	79	76		82	78	76		81
10	88	81	77	74	87	81	77	74	80	76	74		79	76	74		79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1354519
5°	1314106
10°	1171789
15°	827791
20°	399291
25°	129419
30°	36411
35°	14616
40°	4122
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303570

CATALOG NUMBER: P3DUS17R359035DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	548.3	29.7
10°-20°	963.7	52.1
20°-30°	296.2	16.0
30°-40°	38.5	2.1
40°-50°	2.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1808.1	97.8
0°-40°	1846.6	99.9
0°-60°	1849.0	100.0
0°-90°	1849.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1849.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6177	
5°	5970	548
15°	3646	964
25°	535	296
35°	55	39
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303570

CATALOG NUMBER: P3DUS17R359035DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6177.1
2.5°	6128.2
5°	5970.0
7.5°	5708.3
10°	5262.6
12.5°	4566.7
15°	3646.4
17.5°	2645.7
20°	1711.1
22.5°	992.1
25°	534.9
27.5°	281.8
30°	143.8
32.5°	86.3
35°	54.6
37.5°	34.5
40°	14.4
42.5°	5.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)