

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303590

Luminaire Tested: P3DUS24R259035D010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1303590  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-87)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS24R259035D010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2801.0 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1303590  
CATALOG NUMBER: P3DUS24R259035D010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1303590  
 CATALOG NUMBER: P3DUS24R259035D010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	97	95	94
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92	97	95	94
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90	95	93	91
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88	93	91	89
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86	91	89	87
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84	89	87	85
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82	87	85	83
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	80	86	83	81
10	92	86	83	80	91	86	82	80	85	82	80	84	82	80	84	81	80	79	84	81	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3231254
5°	2993103
10°	2253777
15°	1047407
20°	329612
25°	127483
30°	36993
35°	11859
40°	3807
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1303590  
 CATALOG NUMBER: P3DUS24R259035D010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1188.0	42.4
10°-20°	1309.4	46.7
20°-30°	268.9	9.6
30°-40°	32.7	1.2
40°-50°	2.0	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2766.3	98.8
0°-40°	2799.0	99.9
0°-60°	2801.0	100.0
0°-90°	2801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2801.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14736	
5°	13598	###
15°	4614	1309
25°	527	269
35°	44	33
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303590  
CATALOG NUMBER: P3DUS24R259035D010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14735.7
2.5°	14452.3
5°	13597.7
7.5°	12167.6
10°	10121.9
12.5°	7456.4
15°	4613.8
17.5°	2510.6
20°	1412.5
22.5°	863.4
25°	526.9
27.5°	296.7
30°	146.1
32.5°	66.4
35°	44.3
37.5°	26.6
40°	13.3
42.5°	4.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)